

# DATASHEET FG-110C

## EL-FLOW Prestige FG-110C

High Performance Mass Flow Meter for Gases



### Gas Mass Flow Meters for lowest flow rates

Bronkhorst® model FG-110C High Performance Mass Flow Meters (MFMs) are suited for precise measurement of flow ranges between 0,014...0,7 ml<sub>n</sub>/min and 0,18...9 ml<sub>n</sub>/min at operating pressures between vacuum and 100 bar. The MFM consists of a thermal mass flow sensor and a microprocessor based pc-board with signal and fieldbus conversion and a PID controller for optional mass flow control by means of a separately mounted control valve.

EL-FLOW® Prestige series are equipped with a digital pc-board, offering high accuracy, excellent temperature stability and fast response. The main digital pc-board contains all of the general functions needed for measurement and control. In addition to the standard RS232 output the instruments also offer analog I/O. As an option, an on-board interface can be mounted to provide CANopen®, DeviceNet™, EtherCAT®, PROFIBUS DP, PROFINET, Modbus RTU, ASCII or TCP/IP, EtherNet/IP, POWERLINK or FLOW-BUS protocols. The EL-FLOW® Prestige design features standard Multi Gas / Multi Range functionality, providing (OEM-) customers with optimal flexibility and process efficiency.

### Technical specifications

#### Measurement / control system

Flow range (intermediate ranges available)	min. 0,014...0,7 ml <sub>n</sub> /min max. 0,18...9 ml <sub>n</sub> /min (based on N <sub>2</sub> )
Accuracy (incl. linearity) (based on actual calibration)	standard: ±0,5% Rd plus ±0,1%FS (±0,8% Rd plus ±0,2% FS for ranges 3...5 mln/min; ±1% Rd plus ±1% FS for ranges < 3 mln/min)
Repeatability	< 0,2 % RD
Turndown ratio	1:150 (1:50 in analog mode)
Multi Gas / Multi Range	embedded gas data for <u>100 unique gases</u> , plus any mixture of maximum 5 of these gases. MG/MR functionality available up to 100 bar.
Operating temperature	-10 ... 70 °C
Temperature sensitivity	zero: < 0,02% FS/°C; span: < 0,025% Rd/°C
Pressure sensitivity	<0,15% Rd/bar typical N <sub>2</sub> ; < 0,02% Rd/bar N <sub>2</sub> (incl. pressure correction option)
Leak integrity, outboard	tested < 2 x 10 <sup>-9</sup> mbar l/s He
Attitude sensitivity	max. error at 90° off horizontal 0,07% FS at 1 bar, typical N <sub>2</sub>
Warm-up time	30 min. for optimum accuracy 2 min. for accuracy ± 1% FS

#### Mechanical parts

Material (wetted parts)	Stainless steel 316L or comparable, degreased for use on oxygen (O <sub>2</sub> )
-------------------------	---

Mechanical parts

Pressure rating (PN)	100 bar g
Process connections	compression type or face seal (VCR/VCO) couplings
Seals	standard: Viton® options: EPDM, Kalrez® (FFKM), FDA and USP Class VI approved compounds
Weight	0,5 kg
Ingress protection	IP40

Electrical properties

Power supply	+15 ... 24 Vdc			
Max. power consumption meter	Supply	at voltage I/O	at current I/O	extra for fieldbus
	15 V	69 mA	92 mA	<75 mA
	24 V	45 mA	63 mA	<50 mA
Max. Power consumption controller	Supply	at voltage I/O	at current I/O	extra for fieldbus
	15 V	202 mA	225 mA	<75 mA
	24 V	128 mA	146 mA	<50 mA
(based on normally closed valve, pin 5 not used)				
Analog output	0...5 (10) Vdc or 0 (4)...20 mA (sourcing output)			
Digital communication	standard: RS232; options: PROFIBUS DP, CANopen®, DeviceNet™, PROFINET, EtherCAT®, Modbus RTU, ASCII or TCP/IP, EtherNet/IP, POWERLINK, FLOW-BUS			

Electrical connection

Analog/RS232	9-pin D-connector (male);
PROFIBUS DP	bus: 9-pin D-connector (female); power: 9-pin D-connector (male);
CANopen® / DeviceNet™	5-pin M12-connector (male);
FLOW-BUS/Modbus-RTU/ASCII	RJ45 modular jack
Modbus TCP / EtherNet/IP / POWERLINK	2 x RJ45 modular jack (in/out);
EtherCAT®/ PROFINET	2 x RJ45 modular jack (in/out)
CE	EMC 2014/30/EU, RoHS 2011/65/EU
IEC 61010-1	IEC-61010-1:2010 including national deviations for UL (61010-1:2012) and CSA (C22.2 No. 61010-1-12)

Control valve options

External actuator options to be connected to the controller

Ex-proof specifications

Approvals / certificates

## Recommended accessories



### E-8000 SERIES

#### Digital Readout / Control Systems

Bright, wide angle, 1.8" display (TFT technology)

User friendly operation, menu driven with 4 push buttons



### BRIGHT SERIES

#### Compact Local R/C Module

Bright, wide angle, 1.8" display

User friendly operation

Indication/operation/configuration



### PIPS SERIES

#### Plug-in Power Supply

For lab-style or industrial devices

Interchangeable plugs (Euro, UK, USA, Australian, IEC) for mains connection



### IN-LINE FILTER SERIE M-410 RS

1/8" female in / male out

100 bar

Average porosity 0.5...15 µm

## Related products



### EL-FLOW PRESTIGE FG-111B

Min. flow 0,14...7 mln/min

Max. flow 0,4...20 lln/min

Pressure rating 100 bar

100 selectable gases

Customized I/O configurations



### EL-FLOW PRESTIGE FG-200CV

Min. flow 0,014...0,7

mln/min

Max. flow 0,18...9 mln/min

Pressure rating 64 bar

100 selectable gases

Customized I/O configurations



### EL-FLOW PRESTIGE FG-110CP (P-INSENSITIVE)

Min. flow 0,014...0,7

mln/min

Max. flow 0,18...9 mln/min

Pressure rating 100 bar

On-board pressure correction

100 selectable gases



**BRONKHORST (UK) LTD**

1 Kings Court

Willie Snaith Road

Newmarket Suffolk CB8 7TG

Tel. +44 1223 833222

[sales@bronkhorst.co.uk](mailto:sales@bronkhorst.co.uk)

