

# DATASHEET F-112AC

## EL-FLOW Select F-112AC

Digital Thermal Mass Flow Meter for Gases



### Gas Mass Flow Meters for medium flow rates

Bronkhorst® model F-112AC Mass Flow Meters (MFM) are suited for precise measurement of flow ranges between 0,8...40 l<sub>n</sub>/min and 1,4...250 l<sub>n</sub>/min at operating pressures between vacuum and 100 bar. The MFM consists of a thermal mass flow sensor and a microprocessor based pc-board with signal and fieldbus conversion and a PID controller for optional mass flow control by means of a separately mounted control valve.

EL-FLOW® Select series are equipped with a digital pc-board, offering high accuracy, excellent temperature stability and fast response. The main digital pc-board contains all of the general functions needed for measurement and control. In addition to the standard RS232 output the instruments also offer analog I/O. As an option, an on-board interface can be mounted to provide CANopen®, DeviceNet™, EtherCAT®, PROFIBUS DP, PROFINET, Modbus RTU, ASCII or TCP/IP, EtherNet/IP, POWERLINK or FLOW-BUS protocols. The EL-FLOW® Select design features optional Multi Gas / Multi Range functionality, providing (OEM-) customers with optimal flexibility and process efficiency.

### Technical specifications

#### Measurement / control system

Flow range (intermediate ranges available)	min. 0,8...40 l <sub>n</sub> /min max. 1,4...250 l <sub>n</sub> /min (based on N <sub>2</sub> )
Accuracy (incl. linearity) (based on actual calibration)	± 0,5 % RD plus ±0,1% FS
Repeatability	< 0,2 % RD
Turndown ratio	up to 1:187,5 (1:50 in analog mode)
Multi fluid capability	storage of max. 8 calibration curves; optional Multi Gas / Multi Range functionality up to 10 bar abs
Response time (sensor)	typical 0,5 sec.
Operating temperature	-10 ... +70 °C
Temperature sensitivity	zero: < 0,05% FS/°C; span: < 0,05% Rd/°C
Pressure sensitivity	< 0,1% Rd/bar typical N <sub>2</sub> ; 0,01% Rd/bar typical H <sub>2</sub>
Leak integrity, outboard	tested < 2 x 10 <sup>-9</sup> mbar l/s He
Attitude sensitivity	max. error at 90° off horizontal 0,2% at 1 bar, typical N <sub>2</sub>
Warm-up time	30 min. for optimum accuracy 2 min. for accuracy ± 2% FS

#### Mechanical parts

Material (wetted parts)	Stainless steel 316L or comparable
-------------------------	------------------------------------

## Mechanical parts

Pressure rating (PN)	100 bar abs
Process connections	compression type or face seal (VCR/VCO) couplings
Seals	standard: Viton®; options: EPDM, Kalrez® (FFKM)
Weight	1,3 kg
Ingress protection	IP40

## Electrical properties

Power supply	+15 ... 24 Vdc			
Max. power consumption meter	Supply	at voltage I/O	at current I/O	extra for fieldbus
	15 V	95 mA	125 mA	<75 mA
	24 V	65 mA	85 mA	<50 mA
Max. Power consumption controller	Supply	at voltage I/O	at current I/O	extra for fieldbus
	15 V	290 mA	320 mA	<75 mA
	24 V	200 mA	215 mA	<50 mA
Analog output	0...5 (10) Vdc or 0 (4)...20 mA (sourcing output)			
Digital communication	standard: RS232; options: PROFIBUS DP, CANopen®, DeviceNet™, PROFINET, EtherCAT®, Modbus RTU, ASCII or TCP/IP, EtherNet/IP, POWERLINK, FLOW-BUS			

## Electrical connection

Analog/RS232	9-pin D-connector (male);
PROFIBUS DP	bus: 9-pin D-connector (female); power: 9-pin D-connector (male);
CANopen® / DeviceNet™	5-pin M12-connector (male);
FLOW-BUS/Modbus-RTU/ASCII	RJ45 modular jack
Modbus TCP / EtherNet/IP / POWERLINK	2 x RJ45 modular jack (in/out);
EtherCAT®/ PROFINET	2 x RJ45 modular jack (in/out)

## Control valve options

## External actuator options to be connected to the controller

## Ex-proof specifications

## Approvals / certificates

Technical specifications subject to change without notice.

For dimensional drawings and hook-up diagrams please visit the [product page](#) on our [website](#)

Recommended accessories



E-8000 SERIES

Digital Readout / Control Systems

Bright, wide angle, 1.8" display (TFT technology)  
User friendly operation, menu driven with 4 push buttons



BRIGHT SERIES

Compact Local R/C Module

Bright, wide angle, 1.8" display  
User friendly operation  
Indication/operation/configuration



PIPS SERIES

Plug-in Power Supply

For lab-style or industrial devices  
Interchangeable plugs (Euro, UK, USA, Australian, IEC) for mains connection



IN-LINE FILTER  
SERIE M-422 RS

1/4" female in / male out  
200 bar  
Average porosity 2...20 µm

Related products



EL-FLOW SELECT F-111AC

Min. flow 0,4...20 l/min  
Max. flow 0,6...100 l/min  
Pressure rating 100 bar  
Compact design  
High accuracy



EL-FLOW SELECT F-202AV

Min. flow 0,8...40 l/min  
Max. flow 5...250 l/min  
Pressure rating 64 bar  
Compact design  
High accuracy and repeatability



EL-FLOW SELECT F-113AC

Min. flow 4...200 l/min  
Max. flow 8...1670 l/min  
Pressure rating 100 bar  
Compact design  
High accuracy



EL-FLOW SELECT F-122M

Min. flow 0,3...15 l/min  
Max. flow 5...250 l/min  
Pressure rating 200 bar  
Compact design  
High accuracy



**BRONKHORST (UK) LTD**

1 Kings Court

Willie Snaith Road

Newmarket Suffolk CB8 7TG

Tel. +44 1223 833222

[sales@bronkhorst.co.uk](mailto:sales@bronkhorst.co.uk)

