

F-111AX

EX-FLOW F-111AX

Ex-Proof Mass Flow Meter for Gases

- ATEX approval Cat.2, Zone 1
- Also IECEx, TIIS and KCs certified
- High accuracy, excellent repeatability
- Virtually pressure and temperature independent
- Compact design



Intrinsically Safe Gas Mass Flow Meters for low/medium flow rates

Bronkhorst® EX-FLOW Mass Flow Meters (MFM) are suited for precise gas flow measurement in ATEX Zone 1 hazardous areas. The MFM should be connected to a power supply with galvanic isolation / preamplifier / readout system (located in the safe zone). See Bronkhorst® [E-8000 Series](#).

EX-FLOW model F-111AX covers flow ranges from 0,1...5 l_n/min up to 2...100 l_n/min (N₂-equivalent) at operating pressures up to 100 bar.

The intrinsically safe measuring head of the flow meter is tested according to ATEX 114 Directive 2014/34/EU and approved under EC-Type Examination Number: KEMA 01ATEX1172, protection II 2 G Ex ib IIC T4 Gb.

Other certifications: IECEx (IECEx DEK14.0060), TIIS (検・第TC21584号) and KCs = Ex ib IIC T4.

Technical specifications

Measurement / control system

Flow range (intermediate ranges available)	min. 0,1...5 I _N /min max. to 2...100 I _N /min (based on N ₂)
Accuracy (incl. linearity) (based on actual calibration)	± 1 % FS
Repeatability	< 0,2 % RD
Turndown ratio	1:50 (2...100%)
Time constant	5 sec.
Operating temperature	-10 ... +70 °C
Temperature sensitivity	zero: < 0,05% FS/°C; span: < 0,05% Rd/°C
Leak integrity, outboard	tested < 2 x 10 ⁻⁹ mbar l/s He
Attitude sensitivity	max. error at 90° off horizontal 0,2% FS at 1 bar, typical N ₂
Warm-up time	30 min. for optimum accuracy 2 min. for accuracy ± 2% FS

Mechanical parts

Material (wetted parts)	Stainless steel 316L or comparable
Pressure rating (PN)	100 bar abs
Process connections	compression type or face seal (VCR/VCO) couplings
Seals	standard: Viton®; options: EPDM, Kalrez® (FFKM), FDA and USP Class VI approved compounds
Ingress protection	IP65

Electrical properties

Signal circuit	type of explosion protection: intrinsic safety Ex ib IIC, only for connection to a certified intrinsically safe circuit with the following maximum values: U _i = 28 V, I _i = 98 mA, P _i = 686 mW The effective internal capacitance between: Terminals 1 and 3: C _i = 1 nF; Effective internal inductance: L _i = 0,3 mH
Output signal	15 ... 20 mA (linear)
I/O signals via PS/Readout (located in safe area)	analog: 0...5 Vdc, 0...10 Vdc, 0...20 mA, 4...20 mA; digital: RS232, PROFIBUS DP, DeviceNet™, Modbus RTU or ASCII, PROFINET, EtherCAT®, FLOW-BUS

Electrical connection

Ex-proof measuring head	Terminal connection, cable gland M16x1,5
-------------------------	------------------------------------------

Technical specifications subject to change without notice.

For dimensional drawings and hook-up diagrams please visit the [product page](#) on our [website](#)

Recommended accessories



E-8000 SERIES

Digital Readout / Control Systems

- Bright, wide angle, 1.8" display (TFT technology)
- User friendly operation, menu driven with 4 push buttons

IN-LINE FILTER
SERIE M-411 RS

- 1/4" female in / male out
- 100 bar
- Average porosity 0.5...15 µm

Related products



EX-FLOW F-111BX

- Flow ranges from 0,3...15 mln/min up to 0,4...20 ln/min
- Pressure rating 100 bar
- ATEX approval Cat.2, Zone 1
- Rugged IP65 construction



EX-FLOW F-112AX

- Flow ranges from 0,8...40 ln/min up to 5...250 ln/min
- Pressure rating 100 bar
- ATEX approval Cat.2, Zone 1
- Rugged IP65 construction



EX-FLOW F-201AX

- Flow ranges from 0,1...5 ln/min up to 2...100 ln/min
- Pressure rating 64 bar
- ATEX approval Cat.2, Zone 1
- Rugged IP65 construction



BRONKHORST (UK) LTD

1 Kings Court

Willie Snaith Road

Newmarket Suffolk CB8 7TG

Tel. +44 1223 833222

sales@bronkhorst.co.uk

