

F-201CX

EX-FLOW F-201CX

Ex-Proof Mass Flow Controller for Gases

- ATEX approval Cat.2, Zone 1
- High accuracy, excellent repeatability
- Virtually pressure and temperature independent
- Compact design



Intrinsically Safe Gas Mass Flow Controllers for low flow rates

Bronkhorst® EX-FLOW Mass Flow Controllers (MFCs) are suited for precise gas flow control in ATEX Zone 1 hazardous areas. The flow meter part and the control valve of the MFC should be connected (via separate cables) to a power supply with galvanic isolation / preamplifier / readout system (located in the safe zone) which contains a controller board to complete the control loop. See Bronkhorst® [E-8000 Series](#).

EX-FLOW model F-201CX covers flow ranges from 0,3...15 ml_N/min up to 0,4...20 l_N/min (N₂-equivalent) at operating pressures up to 64 bar.

The intrinsically safe measuring head of the flow meter is tested according to ATEX 114 Directive 2014/34/EU and approved under EC-Type Examination Number: KEMA 01ATEX1172, protection II 2 G Ex ib IIC T4 Gb.

The intrinsically safe valve coils are explosion proof certified and available in two options (ATEX certification only):

Coil XB: protection II 1 G Ex ia IIC T6 / protection II 1 D Ex ta IIIC T80°C

Coil XC: protection II 2 G Ex eb IIC T4 / protection II 2 D Ex tb IIIC T130°C

Technical specifications

Measurement / control system

Flow range (intermediate ranges available)	min. 0,3...15 ml _n /min max. 0,4...20 l _n /min (based on N ₂)
Accuracy (incl. linearity) (based on actual calibration)	± 1 % FS
Repeatability	< 0,2 % RD
Turndown ratio	1:50 (2...100%)
Time constant	5 sec.
Control stability	< ± 0,1 % FS typical
Operating temperature	-10 ... +65 °C
Temperature sensitivity	zero: < 0,05% FS/°C; span: < 0,05% Rd/°C
Max. Kv-value	Valve with XB-coil: 4,3 x 10 ⁻³ / Valve with XC-coil: 6,6 x 10 ⁻²
Leak integrity, outboard	tested < 2 x 10 ⁻⁹ mbar l/s He
Attitude sensitivity	max. error at 90° off horizontal 0,2% FS at 1 bar, typical N ₂
Warm-up time	30 min. for optimum accuracy 2 min. for accuracy ± 2% FS

Mechanical parts

Material (wetted parts)	Stainless steel 316L or comparable
Pressure rating (PN)	64 bar abs
Process connections	compression type or face seal (VCR/VCO) couplings
Seals	standard: Viton®; options: EPDM, Kalrez® (FFKM), FDA and USP Class VI approved compounds
Weight	1,7 kg
Ingress protection	IP65

Electrical properties

Signal circuit	type of explosion protection: intrinsic safety Ex ib IIC, only for connection to a certified intrinsically safe circuit with the following maximum values: Ui = 28 V, li = 98 mA, Pi = 686 mW The effective internal capacitance between: Terminals 1 and 3: Ci = 1 nF; Effective internal inductance: Li = 0,3 mH
Output signal	15 ... 20 mA (linear)
I/O signals via PS/Readout (located in safe area)	analog: 0...5 Vdc, 0...10 Vdc, 0...20 mA, 4...20 mA; digital: RS232, PROFIBUS DP, DeviceNet™, Modbus RTU or ASCII, PROFINET, EtherCAT®, FLOW- BUS
XB-coil	Coil voltage max. 28 V/110 mA; 295 Ohm at 20°C
XC-coil	Coil voltage max. 24 V; 65 Ohm at 20°C, Pmax = 9 W at 20°C

Electrical connection

Ex-proof measuring head	Terminal connection, cable gland M16x1,5
Control valve coil	cable gland M20x1,5

Technical specifications subject to change without notice.

For dimensional drawings and hook-up diagrams please visit the [product page](#) on our [website](#)

Recommended accessories



E-8000 SERIES

Digital Readout / Control Systems

Bright, wide angle, 1.8" display (TFT technology)

User friendly operation, menu driven with 4 push buttons



IN-LINE FILTER SERIE M-411 RS

1/4" female in / male out

100 bar

Average porosity 0.5...15 µm

Related products



EX-FLOW F-200CX

Min. flow 0,18...9,5 mln/min
Max. flow 0,18...9,5 mln/min
Pressure rating 64 bar
ATEX approval Cat.2, Zone 1
Rugged IP65 construction



EX-FLOW F-111BX

Flow ranges from 0,3...15 mln/min up to
0,4...20 lln/min
Pressure rating 100 bar
ATEX approval Cat.2, Zone 1
Rugged IP65 construction



EX-FLOW F-211AX

Flow ranges from 0,1...5 lln/min up to 2...
100 lln/min
Pressure rating 100 bar
ATEX approval Cat.2, Zone 1
Rugged IP65 construction



BRONKHORST (UK) LTD

1 Kings Court

Willie Snaith Road

Newmarket Suffolk CB8 7TG

Tel. [+44 1223 833222](tel:+441223833222)

sales@bronkhorst.co.uk

