

# DATASHEET F-103DI

## LOW- $\Delta$ P-FLOW F-103DI

Mass Flow Meter for low pressure drop or corrosive gas service, industrial style



### Thermal Mass Flow Meters for low pressure drop or corrosive gas applications, industrial style

Bronkhorst® model F-103DI Mass Flow Meters (MFMs) are suited for precise measurement of flow ranges between 0,8...40 I<sub>n</sub>/min and 3...150 I<sub>n</sub>/min (N<sub>2</sub>-equivalent). The instruments are particularly suited for corrosive gases or applications with very low differential pressure ( $\Delta$ P). Compared to conventional instruments, LOW- $\Delta$ P-FLOW meters have larger flow channels to minimize the risk of clogging, facilitate cleaning and purging, and cause lower pressure drop (the sensor only requires 0,5 to 5 mbar). This model is of rugged design (IP65) for use in industrial environments or even Zone 2 hazardous areas, with optional ATEX Cat. 3 or FM Class I, Div. 2 approval.

The integrated digital pc-board provides signal and fieldbus conversion as well as PID controller functionality for optional mass flow control by means of a (separately mounted) control valve. In addition to the standard RS232 output the instruments also offer analog I/O. As an option, an on-board interface can be mounted to provide CANopen®, DeviceNet™, EtherCAT®, PROFIBUS DP, PROFINET, Modbus RTU, ASCII or TCP/IP, EtherNet/IP, POWERLINK or FLOW-BUS protocols.

### Technical specifications

#### Measurement / control system

Flow range (intermediate ranges available)	min. 0,8...40 I <sub>n</sub> /min max. 3...150 I <sub>n</sub> /min (based on N <sub>2</sub> )
Accuracy (incl. linearity) (based on actual calibration)	± 1 % FS
Repeatability	< 0,2 % RD
Turndown ratio	1:50 (2...100%)
Max. operating pressure	10 bar g
Multi fluid capability	Storage of max. 8 calibration curves
Response time (sensor)	1 ... 2 sec.
Operating temperature	-10 ... +70 for ATEX cat. 3 and FM Class 1 Div 2 : 0...50°C
Mounting	horizontal
Temperature sensitivity	< 0,1% FS/°C
Pressure sensitivity	0,1 % 0,1% Rd/bar typical N <sub>2</sub>
Leak integrity, outboard	tested < 2 x 10 <sup>-9</sup> mbar l/s He
Warm-up time	30 min. for optimum accuracy 2 min for accuracy ± 2% FS

#### Mechanical parts

Material (wetted parts)	stainless steel 316L or comparable; other on request
Process connections	compression type or face seal (VCR/VCO) couplings
Seals	standard: Viton®; options: EPDM, Kalrez® (FFKM), FDA and USP Class VI approved compounds
Weight	4,4 kg
Ingress protection	IP65

### Electrical properties

Power supply	+15 ... 24 Vdc			
Max. power consumption meter	Supply	at voltage I/O	at current I/O	extra for fieldbus
	15 V	95 mA	125 mA	<75 mA
	24 V	65 mA	85 mA	<50 mA
Max. Power consumption controller	Supply	at voltage I/O	at current I/O	extra for fieldbus
	15 V	290 mA	320 mA	<75 mA
	24 V	200 mA	215 mA	<50 mA
Analog output	0...5 (10) Vdc or 0 (4)...20 mA (sourcing output)			
Digital communication	standard: RS232; options: CANopen®, DeviceNet™, EtherCAT®, PROFIBUS DP, PROFINET, Modbus RTU, ASCII or TCP/IP, EtherNet/IP, POWERLINK or FLOW-BUS			

### Electrical connection

Analog/RS232	8 DIN (male);
PROFIBUS DP	bus: 5-pin M12 (female); power: 8 DIN (male);
CANopen® / DeviceNet™	5-pin M12 (male);
FLOW-BUS/Modbus-RTU/ASCII	5-pin M12 (male)
Modbus TCP / EtherNet/IP / POWERLINK	bus: 2 x 5-pin M12 (female) (in/out); power: 8 DIN (male);
EtherCAT® / PROFINET	bus: 2 x 5-pin M12 (female) (in/out); power: 8 DIN (male)
IEC 61010-1	IEC-61010-1:2010 including national deviations for UL (61010-1:2012) and CSA (C22.2 No. 61010-1-12)

### Control valve options

### External actuator options to be connected to the controller

### Ex-proof specifications

### Approvals / certificates

Technical specifications subject to change without notice.

For dimensional drawings and hook-up diagrams please visit the [product page](#) on our [website](#)

## Recommended accessories



**E-8000 SERIES**

**Digital Readout / Control Systems**

Bright, wide angle, 1.8" display (TFT technology)  
User friendly operation, menu driven with 4 push buttons



**BRIGHT SERIES**

**Compact Local R/C Module**

Bright, wide angle, 1.8" display  
User friendly operation  
Indication/operation/configuration



**PIPS SERIES**

**Plug-in Power Supply**

For lab-style or industrial devices  
Interchangeable plugs (Euro, UK, USA, Australian, IEC) for mains connection



**IN-LINE FILTER SERIE M-423 RS**

1/2" female in / male out  
200 bar  
Average porosity 2...40 µm

## Related products



**LOW-ΔP-FLOW F-102EI**

Min. flow 0,17...8,5 l/min  
Max. flow 1...50 l/min  
Pressure rating up to 10 bar  
Low ΔP, easy to purge  
Compact IP65 design



**LOW-ΔP-FLOW F-103EI**

Min. flow 0,9...45 l/min  
Max. flow 4...200 l/min  
Pressure rating up to 10 bar  
Low ΔP, easy to purge  
Compact IP65 design



**LOW-ΔP-FLOW F-103D**

Min. flow 0,8...40 l/min  
Max. flow 3...150 l/min  
Pressure rating up to 10 bar  
Very low pressure drop  
Suitable for corrosive gases



**BRONKHORST (UK) LTD**

1 Kings Court

Willie Snaith Road

Newmarket Suffolk CB8 7TG

Tel. [+44 1223 833222](tel:+441223833222)

[sales@bronkhorst.co.uk](mailto:sales@bronkhorst.co.uk)

