

# F-202DV

---

## LOW- $\Delta$ P-FLOW F-202DV

Mass Flow Controller for low pressure drop or corrosive gas service

- Large bore capillary (thermal bypass sensor)
- Very low pressure drop
- Less sensitivity to humidity or dirt
- Suitable of corrosive gases
- Easy to purge



---

### Thermal Mass Flow Controllers for low pressure drop or corrosive gas applications

Bronkhorst® model F-202DV Mass Flow Controllers (MFCs) are suited for precise measurement of flow ranges between 0,28...14 l<sub>n</sub>/min and 0,5...25 l<sub>n</sub>/min (N<sub>2</sub>-equivalent). The instruments are particularly suited for corrosive gases or applications with very low differential pressure ( $\Delta$ P). Compared to conventional instruments, LOW- $\Delta$ P-FLOW MFCs have larger flow channels to minimize the risk of clogging, facilitate cleaning and purging, and cause lower pressure drop (the sensor only requires 0,5 to 5 mbar).

The integrated digital pc-board provides signal and fieldbus conversion as well as PID controller functionality for mass flow control by means of the integrated control valve. In addition to the standard RS232 output the instruments also offer analog I/O. As an option, an on-board interface can be mounted to provide CANopen®, DeviceNet™, EtherCAT®, PROFIBUS DP, PROFINET, Modbus RTU, ASCII or TCP/IP, EtherNet/IP or FLOW-BUS protocols.

---

### Technical specifications

Measurement / control system

Flow range (intermediate ranges available)	min. 0,28...14 I <sub>N</sub> /min max. 0,5...25 I <sub>N</sub> /min (based on N <sub>2</sub> )			
Accuracy (incl. linearity) (based on actual calibration)	± 1 % FS			
Repeatability	< 0,2 % RD			
Turndown ratio	1:50 (2...100%)			
Max. operating pressure	10 bar g			
Multi fluid capability	storage of max. 8 calibration curves			
Settling time (in control, typical)	2 ... 3 sec.			
Control stability	< ± 0,1 % FS (typical)			
Operating temperature	-10 ... +70			
Mounting	horizontal			
Temperature sensitivity	< 0,1% FS/°C			
Pressure sensitivity	0,1% Rd/bar typical N <sub>2</sub>			
Max. Kv-value	6,6 x 10 <sup>-2</sup>			
Leak integrity, outboard	tested < 2 x 10 <sup>-9</sup> mbar l/s He			
Warm-up time	30 min. for optimum accuracy 2 min for accuracy ± 2% FS			

Mechanical parts

Material (wetted parts)	stainless steel 316L or comparable; other on request			
Process connections	compression type or face seal (VCR/VCO) couplings			
Seals	standard: Viton®; options: EPDM, Kalrez® (FFKM), FDA and USP Class VI approved compounds			
Weight	0,8 kg			
Ingress protection	IP40			

Electrical properties

Power supply	+15 ... 24 Vdc			
Max. power consumption	Supply	at voltage I/O	at current I/O	extra for fieldbus
	15 V	290 mA	320 mA	<75 mA
	24 V	200 mA	215 mA	<50 mA
Analog output	0...5 (10) Vdc or 0 (4)...20 mA (sourcing output)			
Digital communication	standard: RS232; options: PROFIBUS DP, CANopen®, DeviceNet™, PROFINET, EtherCAT®, Modbus RTU, ASCII or TCP/IP, EtherNet/IP, FLOW-BUS			

**Electrical connection**

Analog/RS232	9-pin D-connector (male);
PROFIBUS DP	bus: 9-pin D-connector (female); power: 9-pin D-connector (male);
CANopen® / DeviceNet™	5-pin M12-connector (male);
FLOW-BUS/Modbus-RTU/ASCII	RJ45 modular jack
Modbus TCP / EtherNet/IP	2 x RJ45 modular jack (in/out);
EtherCAT®/ PROFINET	2 x RJ45 modular jack (in/out);

Technical specifications subject to change without notice.

For dimensional drawings and hook-up diagrams please visit the [product page](#) on our [website](#)

## Recommended accessories



### E-8000 SERIES

#### Digital Readout / Control Systems

Bright, wide angle, 1.8" display (TFT technology)

User friendly operation, menu driven with 4 push buttons



### BRIGHT SERIES

#### Compact Local R/C Module

Bright, wide angle, 1.8" display

User friendly operation

Indication/operation/configuration



### PIPS SERIES

#### Plug-in Power Supply

For lab-style or industrial devices

Interchangeable plugs (Euro, UK, USA, Australian, IEC) for mains connection



### IN-LINE FILTER SERIE M-422 RS

1/4" female in / male out

200 bar

Average porosity 2...20 µm

## Related products



**LOW-ΔP-FLOW F-201EV**

Min. flow 0,028...1,4 l/min  
Max. flow 0,24...12 l/min  
Pressure rating up to 10 bar  
Low ΔP, easy to purge  
Compact design



**LOW-ΔP-FLOW F-202EV**

Min. flow 0,17...8,5 l/min  
Max. flow 1...50 l/min  
Pressure rating up to 10 bar  
Low ΔP, easy to purge  
Compact design



**LOW-ΔP-FLOW F-202DI**

Min. flow 0,28...14 l/min  
Max. flow 0,5...25 l/min  
Pressure rating up to 10 bar  
Low ΔP, easy to purge  
Compact IP65 design



**LOW-ΔP-FLOW F-102D**

Min. flow 0,28...14 l/min  
Max. flow 0,5...25 l/min  
Pressure rating up to 10 bar  
Very low pressure drop  
Suitable for corrosive gases



**BRONKHORST (UK) LTD**

1 Kings Court

Willie Snaith Road

Newmarket Suffolk CB8 7TG

Tel. +44 1223 833222

sales@bronkhorst.co.uk

