

DATASHEET MV-192-HE

MASS-VIEW® MV-192-HE

Helium Flow Meter with integrated display

MASSFLOW-ONLINE PRODUCT



Helium Mass Flow Meters with integrated display

MASS-VIEW® model MV-192-HE Direct Thermal Mass Flow Meters (MFM) are suited for precise measurement of flow ranges between 50...200 ml_n/min and 50...2000 ml_n/min helium at operating pressures up to 10 bar(g). The MFM has an integrated graphical OLED display, clearly visible at wide angles, which allows reading of actual flow (value and a bar graph), total flow and type of gas.

The display features easy set up via a user-friendly menu, using a 4-way navigation push button. Features & functions include a variety of alarm and counter functions, an analog output signal, digital interfaces and two relay contacts.

The MASS-VIEW® series provides modern, novel and economical alternative to variable area meters (VA meters), also known as purge meters. Unlike conventional VA meters these new flow meters measure mass flow instead of volume flow.

Technical specifications

Measurement / control system

Flow range (intermediate ranges available)	min. 50...200 ml _n /min max. 50...2000 ml _n /min (based on helium)
Accuracy (incl. linearity) (based on actual calibration)	± 2% Rd for flow > 50% of max. capacity; ± (1% Rd + 0,5% FS) on lower flows
Repeatability	< 0,2 % FS typical
Turndown ratio	up to 1 : 20
Operating pressure	0 ... 10 bar(g) / 0 ... 150 psi(g)
Pressure coefficient	± 0,2% Rd/bar typical at Air
Standard calibration gas	Helium
Response time (sensor)	2 sec.
Operating temperature	0 ... 50 °C (32 ... 122°F)
Temperature coefficient	Zero: <0,1% FS/°C, Span: <0,2% Rd/°C
Leak integrity, outboard	tested < 2 x 10 ⁻⁹ mbar l/s He
Attitude sensitivity	< 0,1 % FS

Mechanical parts

Material (wetted parts)	Aluminium
-------------------------	-----------

Mechanical parts

Test pressure	21 bar(a) / 300 psi(a)
Process connections	G 1/4" BSPP female thread (compression fittings optional)
Seals	Viton®
Weight	0,7 kg
Ingress protection	IP40

Electrical properties

Power supply	+15 ... 24 Vdc (+/- 10%)
Max. power consumption	approx. 135 mA
Analog output	0 ... 5 Vdc
Digital communication	RS232 / RS485 (Modbus RTU/ASCII)
Min. and max. relay contacts	switching current 0,5 A, 24 Vdc one side grounded (0 Vdc power)
Electrical connection	8-pin RJ-45 modular jack

Electrical connection

Control valve options

External actuator options to be connected to the controller

Ex-proof specifications

Approvals / certificates

Technical specifications subject to change without notice.

For dimensional drawings and hook-up diagrams please visit the [product page](#) on our [website](#)

Related products



MASS-VIEW® MV-102

Min. flow 20...200
mln/min
Max. flow 20...2000
mln/min
Pressure rating 10 bar
Bright, graphical OLED
display
10 pre-installed gases



MASS-VIEW® MV-191-HE

Min. flow 20...50
mln/min He
Max. flow 20...200
mln/min He
Bright, graphical OLED
display
Electr. output, alarm
and counter



MASS-VIEW® MV-194-HE

Min. flow 0,1...2 l/min
He
Max. flow 0,2...20 l/min
He
Bright, graphical OLED
display
Electr. output, alarm
and counter



MASS-VIEW® MV-392-HE

Min. flow 50...200
mln/min He
Max. flow 50...2000
mln/min He
Bright, graphical OLED
display
High quality needle
valve