

MVM-060-PA

MAG-VIEW MVM-060-PA

Low-Flow Magnetic Inductive Flow meters for water-like liquids

- Compact, weatherproof (IP65) design
- No moving parts (no mechanical wear)
- Interference free operation
- Independence to inlet/outlet pipework
- Fast response
- Free pipe cross section: low ΔP , insensitive to contamination
- Analog output (4...20 mA)



MASSFLOW-ONLINE PRODUCT

Electromagnetic flow meters for low flow rates of water and aqueous solutions

MAG-VIEW instruments are electromagnetic inductive flow meters for electrically conductive liquids with a minimum conductivity of 50 $\mu\text{S}/\text{cm}$. The compact, weatherproof (IP65) flow meters do not contain any moving parts, cause virtually no pressure loss and can be mounted in any position, requiring no straight inlet or outlet runs.

MAG-VIEW flow meter model MVM-060-PA has a nominal diameter of DN10 for flow rates of 1...60 l/min, suited for operating pressures up to 16 bar(g). The instrument allows frequency and analog output (4...20 mA) proportional to the flow.

Technical specifications

Measurement / control system

Flow rates	1 ... 60 l/min
Volume flow accuracy	± 1,5 % RD + ±0,3% FS (incl. factory calibration certificate; test conditions: water 23°C)
Turndown ratio	1:60
Reproducibility	1 % FS
Signal output starting from	~ 0,9 l/min
Media	Water and other conductive liquids (minimum conductivity of 50 µS/cm)
Response time (sensor)	< 800 msec
Operating temperature	5 ... 90 °C
Mounting	Any position, attitude insensitive
Flow indication	green LED, flow proportional flashing

Mechanical parts

Material (wetted parts)	Electrodes: Stainless Steel 1.4571 Process connections: Stainless Steel 1.4571 Measuring pipe: PEEK-GF30 Gasket: EPDM
Housing	Aluminium pressure diecasted
Diameter	DN10
Process connections	½" BSP male thread
Ingress protection	IP65
Nominal pressure	PN16

Electrical properties

Power supply	24 Vdc ±10 %
Max. power consumption	≤ 150 mA
Analog output	4...20 mA, max. load 250 Ω to GND
Frequency output	Pulse rate / K-factor : 500 pulses/l Resolution : 2,0 ml/pulse Signal shape : Square wave signal - duty cycle 50:50 Push-Pull - NPN open collector [o.c.] - PNP o.c. Signal current : max. 100 mA, current limited
Electrical connection	5-pin-plug M12x1

Technical specifications subject to change without notice.

*Test conditions
Water 23°C

For dimensional drawings and hook-up diagrams please visit the [product page](#) on our [website](#)

Related products



MAG-VIEW MVM-030-PA

Flow range 0,5 ... 30 l/min
Pressure rating 16 bar
Non-obstructive; low ΔP
No moving parts; long life cycle
Analog output



MAG-VIEW MVM-060-PN

Flow range 1 ... 60 l/min
Pressure rating 16 bar
Non-obstructive; low ΔP
No moving parts; long life cycle
Insensitive to contamination



MAG-VIEW MVM-200-QA

Flow range 10 ... 200 l/min
Pressure rating 10 bar
Non-obstructive; low ΔP
No moving parts; long life cycle
Cost-optimized (plastic) model



MAG-VIEW MVM-250-PA

Flow range 5 ... 250 l/min
Pressure rating 16 bar
Non-obstructive; low ΔP
No moving parts; long life cycle
Analog output



BRONKHORST (UK) LTD

1 Kings Court

Willie Snaith Road

Newmarket Suffolk CB8 7TG

Tel. [+44 1223 833222](tel:+441223833222)

sales@bronkhorst.co.uk

