

ES-FLOW™ ES-113I

Low-Flow Ultrasonic Flow Meter for liquids

- Fast and accurate measuring signal
- Low pressure loss due to straight sensor tube
- Medium independent and temperature insensitive
- Local display with capacitive touchscreen
- IP66/IP67 rating
- Pressure rating 100 bar



Low-Flow Ultrasonic Flow Meters for Liquids

ES-FLOW™ model ES-113I Liquid Flow Meters (LFMs) are suited for precise measurement of volume flow ranges between 2 and 1500 ml/min. The LFM consists of an innovative ultrasonic flow sensor and an IP66/IP67 protected measuring head with bright LCD display and capacitive touchscreen for adjustment of the settings e.g. for flow indication, alarm, totalisation and control (if applicable). The electronics include a PID controller for optional flow control by means of a separately mounted control valve or pump. ES-FLOW™ model ES-113I has orbitally welded compression type connections, making this instrument suitable for operating pressures up to 100 bar.

Bronkhorst® ES-FLOW™ series are equipped with a digital pc-board, offering high accuracy, excellent temperature stability and fast response. The main digital pc-board contains all of the general functions needed for measurement and control. In addition to the standard RS232 output the instruments also offer analog I/O. As an option, an on-board interface can be mounted to provide CANopen®, DeviceNet™, EtherCAT®, PROFIBUS DP, PROFINET, Modbus RTU, ASCII or TCP/IP, EtherNet/IP, POWERLINK or FLOW-BUS protocols.

November 2020, launch of ES-FLOW MkII generation

With the introduction of the second generation of our ES-FLOW series, indicated by suffix MkII, Bronkhorst realised some important improvements and new options. Here are the main MkII-highlights:

- **Hygienic Standards 3-A**

The [ES-103I](#) MkII with Tri-Clamp flanges is authorized by 3-A, meeting the highest hygienic standards.

- **Hygienic Flow Controller**

Combining the ES-FLOW flow meter with a GEMÜ 650 pneumatic diaphragm valve makes an excellent hygienic flow controller for a wide range of applications within the Food & Beverage market. The GEMÜ valve is also 3-A authorized.

- **EC Regulation Nos. 1935/2004 and 2023/2006 (Food Contact Materials)**

By meeting the requirements, Bronkhorst can provide a Manufacturer Declaration for these regulations.

- **Improved accuracy and rangeability**

- **Additional functionalities and EtherNet fieldbus options**

Technical specifications

Measurement / control system

Minimum full scale flow	100 ml/min
Maximum full scale flow	1500 ml/min
Minimum flow	2 ml/min
Volume flow accuracy	Mkl: $\pm 1\%$ Rd $\pm \leq 1$ ml/min; Mkll: $\pm 0,8\%$ Rd $\pm \leq 0,4$ ml/min
Repeatability	$\leq 0,1\%$ Rd $\pm 0,05$ ml/min
Turndown ratio	digital 2:100 up to 2:1500 ml/min (full scale value scalable by the user); analog: 1:50 (2...100%);
Fluids	liquids with sound speed between 1000 and 2000 m/s; fluid independent measurement; also suitable for non-conductive fluids
Response time (sensor)	200 msec (meter, t98%)
Refresh (cycle) time	≤ 10 msec
Fluid temperature max	-10 ... 90 °C Mkll: steam cleaning (SIP) max 140°C
Ambient temperature max	10 ... 60 °C
Mounting	Any position, attitude sensitivity negligible.
Temperature accuracy	± 1 °C

Mechanical parts

Sensor	Straight tube
Material (wetted parts)	stainless steel 316L
Surface quality	Ra < 0,8 μ m
Pressure rating (PN)	10 bara at TAMB = 15...35°C, TAMB - TMED ≤ 25 °C; for elevated temperatures please consult factory
Process connections	3 mm, 6 mm, 1/8", 1/4" OD compression type or 1/4" face seal male (welded)
Seals	none
Weight	Meter: 1,3 kg; Controller: on request
Ingress protection	IP66 and IP67

Electrical properties

Power supply	+15...24 Vdc
Max. power consumption	2.8 W
Analog output	0...5 (10) Vdc, min. load impedance > 2 k Ω ; 0 (4)...20 mA (sourcing), max. load impedance < 375 Ω
Analog setpoint	0...5 (10) Vdc, impedance > 100 k Ω ; 0 (4)...20 mA, impedance ~ 100 Ω
Customised I/O	Analog control signal output: 0...10 Vdc or 4...20 mA; Pulse output; for more options, see Model number identification in our ES-FLOW brochure
Digital communication	Standard RS232; Options: CANopen®, DeviceNet™, EtherCAT®, PROFIBUS DP, PROFINET, Modbus RTU, ASCII or TCP/IP, EtherNet/IP, POWERLINK or FLOW-BUS

Electrical connection

Analog/RS232	8-pin M12 connector (male)
Configured I/O / Actuator output	8-pin M12 Connector (male)
Actuator/Remote display	4-pin M8 connector (female)
PROFIBUS DP	bus: 5-pin M12 connector (female); 8-pin power: M12 connector (male)
CANopen® / DeviceNet™	5-pin M12 connector (male)
FLOW-BUS/Modbus-RTU/ASCII	5-pin M12 connector (male)
Modbus TCP / EtherNet/IP / POWERLINK	2 x 4-pin M12 connector female (in/out)
EtherCAT®/ PROFINET	2 x 4-pin M12 connector female (in/out)
PROFINET	8-pin M12 connector (male)

Approvals / certificates

Food contact	EC 1935/2004
--------------	--------------

Technical specifications subject to change without notice.

For dimensional drawings and hook-up diagrams please visit the [product page](#) on our [website](#)

Related products



ES-FLOW™ ES-103I

Min. flow 2 ... 100 ml/min
Max. flow approx. 1500 ml/min
Pressure rating 10 bar
IP66/IP67 display; touchscreen
Hygienic, flanged type design



ES-FLOW™ ES-FLOW METER WITH PUMP

Min. flow 2 ... 100 ml/min
Max. flow approx. 1500 ml/min
Compact, integrated dosing solution
Direct pump control



BRONKHORST (UK) LTD

1 Kings Court

Willie Snaith Road

Newmarket Suffolk CB8 7TG

Tel. +44 1223 833222

sales@bronkhorst.co.uk