

EL-PRESS P-522C

Digital Electronic Pressure Meter

- For absolute or gauge pressure
- High accuracy and repeatability
- Well proven, compact thru-flow design
- On-board PID controller for pressure control
- Analog, RS232 and fieldbus communication



Digital Electronic Pressure Meters

Bronkhorst® model P-522C Electronic Pressure Transducers (EPTs) are suited for precise measurement of pressure ranges between 2...100 bar and 4...200 bar absolute or gauge. The EPT has a well-proven compact thru-flow design and includes a diaphragm type piezo-resistive pressure sensor, a microprocessor based pc-board with signal and fieldbus conversion and a PID controller for optional pressure control by means of a separately mounted control valve.

EL-PRESS series are equipped with a digital pc-board, offering high accuracy, excellent temperature stability and fast response. The main digital pc-board contains all of the general functions needed for measurement and control. In addition to the standard RS232 output the instruments also offer analog I/O. As an option, an on-board interface can be mounted to provide CANopen®, DeviceNet™, EtherCAT®, PROFIBUS DP, PROFINET, Modbus RTU, ASCII or TCP/IP, EtherNet/IP, POWERLINK or FLOW-BUS protocols.

Technical specifications

Measurement / control system

Absolute pressure sensors	Code: M40A - Ranges (FS): 100 ... 400 bara - P-max: 500 bara
Accuracy (incl. linearity and hysteresis)	standard: ± 0,5 % FS
Repeatability	< 0,1 % RD
Pressure rangeability	1:50 for pressure meter; 1 : 20 for P2-control; 1 : 5 for P1-control
Response time (sensor)	2 msec
Operating temperature	-10 ... +70 °C
Temperature sensitivity	0,1% FS/°C
Leak integrity, outboard	tested < 2 x 10 ⁻⁹ mbar l/s He
Attitude sensitivity	max. error at 90° off horizontal < 0,3 mbar
Warm-up time	negligible

Mechanical parts

Material (wetted parts)	stainless steel 316L or comparable
Process connections	compression type or face seal (VCR/VCO) couplings
Seals	standard: Viton®; options: EPDM, Kalrez® (FFKM)
Weight	0,4 kg
Ingress protection	IP40

Electrical properties

Power supply	+15 ... 24 Vdc			
Max. power consumption meter	Supply	at voltage I/O	at current I/O	extra for fieldbus
	15 V	95 mA	125 mA	<75 mA
	24 V	65 mA	85 mA	<50 mA
Max. Power consumption controller	Supply	at voltage I/O	at current I/O	extra for fieldbus
	15 V	290 mA	320 mA	<75 mA
	24 V	200 mA	215 mA	<50 mA
Analog output	0...5 (10) Vdc or 0 (4)...20 mA (sourcing output)			
Digital communication	standard: RS232; options: CANopen®, DeviceNet™, EtherCAT®, PROFIBUS DP, PROFINET, Modbus RTU, ASCII or TCP/IP, EtherNet/IP, POWERLINK or FLOW-BUS			

Electrical connection

Analog/RS232	9-pin D-connector (male);
PROFIBUS DP	bus: 9-pin D-connector (female); power: 9-pin D-connector (male);
CANopen® / DeviceNet™	5-pin M12-connector (male);
FLOW-BUS/Modbus-RTU/ASCII	RJ45 modular jack
Modbus TCP / EtherNet/IP / POWERLINK	2 x RJ45 modular jack (in/out);
EtherCAT®/ PROFINET	2 x RJ45 modular jack (in/out);

Technical specifications subject to change without notice.

Note: The measuring cell of the pressure sensor is separated from the external pressure by a thin, sensitive stainless steel diaphragm, and the sealed off cavity between diaphragm and cell is filled with oil. Since the standard oil filling is flammable, Bronkhorst advises to take precautions when oxygen or any other explosive fluid is used.

For dimensional drawings and hook-up diagrams please visit the [product page](#) on our [website](#)

Recommended accessories



E-8000 SERIES

Digital Readout / Control Systems

Bright, wide angle, 1.8" display (TFT technology)

User friendly operation, menu driven with 4 push buttons



BRIGHT SERIES

Compact Local R/C Module

Bright, wide angle, 1.8" display

User friendly operation

Indication/operation/configuration



PIPS SERIES

Plug-in Power Supply

For lab-style or industrial devices

Interchangeable plugs (Euro, UK, USA, Australian, IEC) for mains connection

Related products



EL-PRESS P-512C

Min. pressure 1,28...64 bar

Max. pressure 2...100 bar

Absolute or gauge pressure

High accuracy



EL-PRESS P-532C

Min. pressure 4...200 bar

Max. pressure 8...400 bar

Absolute or gauge pressure

High accuracy



IN-PRESS P-522CI

Min. pressure 2...100 bar

Max. pressure 4...200 bar

Absolute or gauge pressure

Compact IP65 design



BRONKHORST (UK) LTD

1 Kings Court

Willie Snaith Road

Newmarket Suffolk CB8 7TG

Tel. +44 1223 833222

sales@bronkhorst.co.uk