

# P-822CV

---

## EL-PRESS P-822CV

### Process Pressure Controller

- Dual valve pressure control (inlet/relief)
- For absolute or gauge pressure
- High accuracy and repeatability
- Low gas consumption (no gas bleed)
- On-board PID controller for pressure control
- Analog, RS232 and fieldbus communication



---

### Process Pressure Controller

Bronkhorst® model P-822CV Process Pressure Controllers (PPCs) are suited for precise pressure control with closed volumes, i.e. with one fluid connection. This PPC model is suited for pressure ranges between 5...100 bar and 10...200 bar absolute. The instrument comprises a diaphragm type piezo-resistive pressure sensor, a microprocessor based pc-board with signal and fieldbus conversion and a PID controller for pressure control by means of two integrated control valves. This dual valve construction is a compact, economical alternative to configurations where forward pressure controllers are combined with separate bleed ports and relief valves. It is considered as a great advantage that the relief valve does not vent to the atmosphere. Furthermore the system can be set for either fast or smooth controlled (de)pressurization.

EL-PRESS series are equipped with a digital pc-board, offering high accuracy, excellent temperature stability and fast response. The main digital pc-board contains all of the general functions needed for measurement and control. In addition to the standard RS232 output the instruments also offer analog I/O. As an option, an on-board interface can be mounted to provide CANopen®, DeviceNet™, EtherCAT®, PROFIBUS DP, PROFINET, Modbus RTU, ASCII or TCP/IP, EtherNet/IP or FLOW-BUS protocols.

## Technical specifications

### Measurement / control system

Pressure ranges	min. 5 ... 100 bar max. 10 ... 200 bar
Accuracy (incl. linearity and hysteresis)	standard: $\pm 0,5$ % FS
Repeatability	< 0,25 % RD
Pressure rangeability	1:20 (with flow range 1:50)
Response time (sensor)	2 msec
Operating temperature	-10 ... +70 °C
Temperature sensitivity	0,1% FS/°C
Leak integrity, outboard	tested < $2 \times 10^{-9}$ mbar l/s He
Attitude sensitivity	max. error at 90° off horizontal < 0,3 mbar
Warm-up time	negligible

### Mechanical parts

Material (wetted parts)	stainless steel 316L or comparable
Process connections	compression type or face seal (VCR/VCO) couplings
Seals	Viton®
Weight	2,3 kg
Ingress protection	IP40

### Electrical properties

Power supply	+15 ... 24 Vdc			
Max. power consumption	Supply	at voltage I/O	at current I/O	extra for fieldbus
	15 V	290 mA	320 mA	<75 mA
	24 V	200 mA	215 mA	<50 mA
Analog output	0...5 (10) Vdc or 0 (4)...20 mA (sourcing output)			
Digital communication	standard: RS232; options: CANopen®, DeviceNet™, EtherCAT®, PROFIBUS DP, PROFINET, Modbus RTU, ASCII or TCP/IP, EtherNet/IP or FLOW-BUS			

### Electrical connection

Analog/RS232	9-pin D-connector (male);
PROFIBUS DP	bus: 9-pin D-connector (female); power: 9-pin D-connector (male);
CANopen® / DeviceNet™	5-pin M12-connector (male);
FLOW-BUS/Modbus-RTU/ASCII	RJ45 modular jack
Modbus TCP / EtherNet/IP	2 x RJ45 modular jack (in/out);
EtherCAT® / PROFINET	2 x RJ45 modular jack (in/out);

Technical specifications subject to change without notice.

**Note:** The measuring cell of the pressure sensor is separated from the external pressure by a thin, sensitive stainless steel diaphragm, and the sealed off cavity between diaphragm and cell is filled with oil. Since the standard oil filling is flammable, Bronkhorst advises to take precautions when oxygen or any other explosive fluid is used.

For dimensional drawings and hook-up diagrams please visit the [product page](#) on our [website](#)

## Recommended accessories



### E-8000 SERIES

#### Digital Readout / Control Systems

Bright, wide angle, 1.8" display (TFT technology)  
User friendly operation, menu driven with 4 push buttons



### BRIGHT SERIES

#### Compact Local R/C Module

Bright, wide angle, 1.8" display  
User friendly operation  
Indication/operation/configuration



### PIPS SERIES

#### Plug-in Power Supply

For lab-style or industrial devices  
Interchangeable plugs (Euro, UK, USA, Australian, IEC) for mains connection

## Related products



**EL-PRESS P-802CV**

Min. pressure 17,5...350 mbar  
Max. pressure 3,2...64 bar  
Absolute or gauge pressure  
Fast or smooth pressure control



**EL-PRESS P-812CV**

Min. pressure 3,2...64 bar  
Max. pressure 5...100 bar  
Absolute or gauge pressure  
Fast or smooth pressure control



**IN-PRESS P-822CI**

Min. pressure 5...100 bar  
Max. pressure 10...200 bar  
Absolute or gauge pressure  
Fast or smooth pressure control  
Rugged IP65 construction



**BRONKHORST (UK) LTD**

1 Kings Court

Willie Snaith Road

Newmarket Suffolk CB8 7TG

Tel. [+44 1223 833222](tel:+441223833222)

[sales@bronkhorst.co.uk](mailto:sales@bronkhorst.co.uk)

