

DATASHEET W-202A

CEM Evaporator W-202A

3-Way Mixing Valve and Evaporator



3-way Mixing Valve and Evaporator

Bronkhorst® model W-202A CEM 3-way Mixing Valve and Evaporator is suited for precise vapor flow delivery, composed by mixing up to 120 g/h H₂O (320 g/h IPA) with max. 10 l_n/min of carrier gas at operating pressures between vacuum and 100 bar. The temperature controlled mixing device is used in combination with a (thermal or Coriolis) liquid flow meter and an MFC for carrier gas, together forming a Controlled Evaporation and Mixing (CEM) System.

Technical specifications

Measurement / control system

Max. heating temperature	200 °C
--------------------------	--------

Heater capacity	100 W
-----------------	-------

Max. Kv-value	$6,6 \times 10^{-2}$
---------------	----------------------

Mechanical parts

Material (wetted parts)	Stainless steel 316L or comparable
-------------------------	------------------------------------

Pressure rating (PN)	100 bar a
----------------------	-----------

Max. ΔP	5 ... 40 bar (depends on Kv-value; contact your distributor for details)
-----------------	---

Process connections	Gas and liquid inlet: compression type or face seal couplings; Vapour outlet: 1/8" tube (other options on request); Purge connection: 1/8" OD or 1/8" face seal
---------------------	---

Seals	Metal-to-metal
-------	----------------

Protection class	IP40
------------------	------

Plunger	Kalrez®; other on request
---------	---------------------------

Connector	Amphenol 6-pin male
-----------	---------------------

Electrical properties

Power supply	Mixing valve: +15...24 Vdc +/-10%; Heater: 44 Vac
--------------	--

Max. power consumption	Mixing valve: 4 W (max.); Heater: 150 W (nominal)
------------------------	--

Electrical connection

Control valve options

External actuator options to be connected to the controller

Ex-proof specifications

Approvals / certificates

Technical specifications subject to change without notice.

For dimensional drawings and hook-up diagrams please visit the [product page](#) on our [website](#)

Recommended accessories



E-8000 SERIES

Digital Readout / Control Systems

Bright, wide angle, 1.8" display (TFT technology)

User friendly operation, menu driven with 4 push buttons

Related products




CEM EVAPORATOR W-101A

Max. 2 g/h liquid;
Max. 4 l/min gas
Pressure rating 100 bar
Very stable vapor flow
Flexible gas/liquid ratio



CEM EVAPORATOR W-102A

Max. 30 g/h liquid;
Max. 4 l/min gas
Pressure rating 100 bar
Very stable vapor flow
Flexible gas/liquid ratio



CEM EVAPORATOR W-303B

Max. 1200 g/h liquid;
Max. 100 l/min gas
Pressure rating 100 bar
Very stable vapor flow
Flexible gas/liquid ratio