


W-303B

CEM EVAPORATOR W-303B

3-Way Mixing Valve and Evaporator

- Accurately controlled gas/liquid mixture
- Fast response
- High reproducibility
- Very stable vapor flow



3-way Mixing Valve and Evaporator

Bronkhorst® model W-303B CEM 3-way Mixing Valve and Evaporator is suited for precise vapor flow delivery, composed by mixing up to 1200 g/h H₂O (3200 g/h IPA) with max. 100 l_n/min of carrier gas at operating pressures between vacuum and 100 bar. The temperature controlled mixing device is used in combination with a (thermal or Coriolis) liquid flow meter and an MFC for carrier gas, together forming a Controlled Evaporation and Mixing (CEM) System.

Technical specifications

Measurement / control system

Max. heating temperature	200 °C
--------------------------	--------

Heater capacity	1000 W
-----------------	--------

Max. Kv-value	$6,6 \times 10^{-2}$
---------------	----------------------

Mechanical parts

Material (wetted parts)	Stainless steel 316L or comparable
-------------------------	------------------------------------

Pressure rating (PN)	100 bar a
----------------------	-----------

Max. ΔP	5 ... 40 bar d (depends on Kv-value; contact your distributor for details)
-----------------	---

Process connections	Gas and liquid inlet: compression type or face seal couplings; Vapour outlet: 1/4" tube (other options on request); Purge connection: 1/8" OD or 1/8" face seal
---------------------	---

Seals	Metal-to-metal
-------	----------------

Protection class	IP40
------------------	------

Plunger	Kalrez®; other on request
---------	---------------------------

Connector	Amphenol 6-pin male
-----------	---------------------

Electrical properties

Power supply	Mixing valve: +/-15...24 Vdc; Heater: 110-120 Vac or 220-240 Vac
--------------	---

Max. power consumption	Mixing valve: 4 W (max.); Heater: 1375 W (nominal)
------------------------	---

Technical specifications subject to change without notice.

For dimensional drawings and hook-up diagrams please visit the [product page](#) on our [website](#)

Recommended accessories



E-8000 SERIES

Digital Readout / Control Systems

Bright, wide angle, 1.8" display (TFT technology)

User friendly operation, menu driven with 4 push buttons

Related products



CEM EVAPORATOR W-101A

Max. 2 g/h liquid;
Max. 4 l/min gas
Pressure rating 100 bar
Very stable vapor flow
Flexible gas/liquid ratio



CEM EVAPORATOR W-102A

Max. 30 g/h liquid;
Max. 4 l/min gas
Pressure rating 100 bar
Very stable vapor flow
Flexible gas/liquid ratio



CEM EVAPORATOR W-202A

Max. 120 g/h liquid;
Max. 10 l/min gas
Pressure rating 100 bar
Very stable vapor flow
Flexible gas/liquid ratio



BRONKHORST (UK) LTD

1 Kings Court

Willie Snaith Road

Newmarket Suffolk CB8 7TG

Tel. [+44 1223 833222](tel:+441223833222)

sales@bronkhorst.co.uk

