

DATASHEET F-111B

EL-FLOW Select F-111B

Digital Thermal Mass Flow Meter for Gases



Gas Mass Flow Meters for low flow rates

Bronkhorst® model F-111B Mass Flow Meters (MFM) are suited for precise measurement of flow ranges between 0,16...8 ml_n/min and 0,16...25 l_n/min at operating pressures between vacuum and 100 bar. The MFM consists of a thermal mass flow sensor and a microprocessor based pc-board with signal and fieldbus conversion and a PID controller for optional mass flow control by means of a separately mounted control valve.

EL-FLOW® Select series are equipped with a digital pc-board, offering high accuracy, excellent temperature stability and fast response. The main digital pc-board contains all of the general functions needed for measurement and control. In addition to the standard RS232 output the instruments also offer analog I/O. As an option, an on-board interface can be mounted to provide CANopen®, DeviceNet™, EtherCAT®, PROFIBUS DP, PROFINET, Modbus RTU, ASCII or TCP/IP, EtherNet/IP, POWERLINK or FLOW-BUS protocols. The EL-FLOW® Select design features optional Multi Gas / Multi Range functionality, providing (OEM-) customers with optimal flexibility and process efficiency.

Technical specifications

Measurement / control system

Flow range (intermediate ranges available)	min. 0,16...8 ml _n /min max. 0,16...25 l _n /min (based on N ₂)
Accuracy (incl. linearity) (based on actual calibration)	± 0,5 % RD plus ±0,1% FS
Repeatability	< 0,2 % RD
Turndown ratio	up to 1:187,5 (1:50 in analog mode)
Multi fluid capability	storage of max. 8 calibration curves; optional Multi Gas / Multi Range functionality up to 10 bar abs
Response time (sensor)	typical 0,5 sec.
Operating temperature	-10 ... +70 °C
Temperature sensitivity	zero: <0,05% FS/°C; span: <0,05% Rd/°C
Pressure sensitivity	< 0,1% Rd/bar typical N ₂ ; 0,01% Rd/bar typical H ₂
Leak integrity, outboard	tested < 2 x 10 ⁻⁹ mbar l/s He
Attitude sensitivity	max. error at 90° off horizontal 0,2% at 1 bar, typical N ₂
Warm-up time	30 min. for optimum accuracy 2 min for accuracy ± 2% FS

Mechanical parts

Material (wetted parts)	Stainless steel 316L or comparable
-------------------------	------------------------------------

Mechanical parts

Pressure rating (PN)	100 bar abs
Process connections	compression type or face seal (VCR/VCO) couplings
Seals	standard: Viton®; options: EPDM, Kalrez® (FFKM), FDA and USP Class VI approved compounds
Weight	0,5 kg
Ingress protection	IP40

Electrical properties

Power supply	+15 ... 24 Vdc			
Max. power consumption meter	Supply	at voltage I/O	at current I/O	extra for fieldbus
	15 V	95 mA	125 mA	<75 mA
	24 V	65 mA	85 mA	<50 mA
Max. Power consumption controller	Supply	at voltage I/O	at current I/O	extra for fieldbus
	15 V	290 mA	320 mA	<75 mA
	24 V	200 mA	215 mA	<50 mA
Analog output	0...5 (10) Vdc or 0 (4)...20 mA (sourcing output)			
Digital communication	standard: RS232; Options: PROFIBUS DP, CANopen®, DeviceNet™, PROFINET, EtherCAT®, Modbus RTU, ASCII or TCP/IP, EtherNet/IP, POWERLINK, FLOW-BUS			

Electrical connection

Analog/RS232	9-pin D-connector (male);
PROFIBUS DP	bus: 9-pin D-connector (female); power: 9-pin D-connector (male);
CANopen® / DeviceNet™	5-pin M12-connector (male);
FLOW-BUS/Modbus-RTU/ASCII	RJ45 modular jack
Modbus TCP / EtherNet/IP / POWERLINK	2 x RJ45 modular jack (in/out)
EtherCAT®/ PROFINET	2 x RJ45 modular jack (in/out)

Control valve options

External actuator options to be connected to the controller

Ex-proof specifications

Approvals / certificates

Technical specifications subject to change without notice.

For dimensional drawings and hook-up diagrams please visit the [product page](#) on our [website](#)

Recommended accessories



E-8000 SERIES

Digital Readout / Control Systems

Bright, wide angle, 1.8" display (TFT technology)

User friendly operation, menu driven with 4 push buttons



BRIGHT SERIES

Compact Local R/C Module

Bright, wide angle, 1.8" display

User friendly operation

Indication/operation/configuration



PIPS SERIES

Plug-in Power Supply

For lab-style or industrial devices

Interchangeable plugs (Euro, UK, USA, Australian, IEC) for mains connection



**IN-LINE FILTER
SERIE M-411 RS**

1/4" female in / male out

100 bar

Average porosity 0.5...15 μm

Related products



EL-FLOW SELECT F-110C

Min. flow 0,014...0,7
mln/min
Max. flow 0,06...9 mln/min
Pressure rating 100 bar
Compact design
High accuracy



EL-FLOW SELECT F-201CV

Min. flow 0,16...8 mln/min
Max. flow 0,5...25 ln/min
Pressure rating 64 bar
Compact design
High accuracy and
repeatability



EL-FLOW SELECT F-111AC

Min. flow 0,4...20 ln/min
Max. flow 0,6...100 ln/min
Pressure rating 100 bar
Compact design
High accuracy



EL-FLOW SELECT F-121M

Min. flow 0,3...15 mln/min
Max. flow 0,4...20 ln/min
Pressure rating 200 bar
Compact design
High accuracy

Related products



EL-FLOW SELECT F-110C

Min. flow 0,014...0,7
mln/min
Max. flow 0,06...9 mln/min
Pressure rating 100 bar
Compact design
High accuracy



EL-FLOW SELECT F-201CV

Min. flow 0,16...8 mln/min
Max. flow 0,5...25 ln/min
Pressure rating 64 bar
Compact design
High accuracy and
repeatability



EL-FLOW SELECT F-111AC

Min. flow 0,4...20 ln/min
Max. flow 0,6...100 ln/min
Pressure rating 100 bar
Compact design
High accuracy



EL-FLOW SELECT F-121M

Min. flow 0,3...15 mln/min
Max. flow 0,4...20 ln/min
Pressure rating 200 bar
Compact design
High accuracy



BRONKHORST USA LLC

57 South Commerce Way

Suite 120

USA - Bethlehem, PA 18017

Tel. [+1-610-866-6750](tel:+1-610-866-6750)

sales@bronkhorstusa.com

