

F-106BX

EX-FLOW F-106BX

Ex-Protected Mass Flow Meter for High Gas Flow

- ATEX approval Cat.2, Zone 1
- Also IECEx, TIIS and KCs certified
- High accuracy, excellent repeatability
- Virtually pressure and temperature independent
- "Wafer type" for mounting between flanges (DN50 / 2")



Intrinsically Safe Gas Mass Flow Meters for high flow rates

Bronkhorst® EX-FLOW Mass Flow Meters (MFMs) are suited for precise gas flow measurement in ATEX Zone 1 hazardous areas. The MFM should be connected to a power supply with galvanic isolation / preamplifier / readout system (located in the safe zone). See Bronkhorst® [E-8000 Series](#).

EX-FLOW model F-106BX covers flow ranges from 1...50 m³_n/h up to 10...500 m³_n/h (N₂-equivalent) at operating pressures up to 40 bar.

The intrinsically safe measuring head of the flow meter is tested according to ATEX 114 Directive 2014/34/EU and approved under EC-Type Examination Number: KEMA 01ATEX1172, protection II 2 G Ex ib IIC T4 Gb.

Other certifications: IECEx (IECEx DEK14.0060), TIIS (検・第TC21584号) and KCs = Ex ib IIC T4.

Technical specifications

Measurement / control system

Flow range (intermediate ranges available)	min. 1...50 m ³ _n /h max. 10...500 m ³ _n /h (based on N ₂)
Accuracy (incl. linearity) (based on actual calibration)	± 1 % FS
Repeatability	< 0,2 % RD
Turndown ratio	1:50 (2...100%)
Time constant	5 sec.
Operating temperature	-10 ... +70 °C
Temperature sensitivity	zero: < 0,05% FS/°C; span: < 0,05% Rd/°C
Leak integrity, outboard	tested < 2 x 10 ⁻⁹ mbar l/s He
Attitude sensitivity	max. error at 90° off horizontal 0,2% FS at 1 bar, typical N ₂
Warm-up time	30 min. for optimum accuracy 2 min. for accuracy ± 2% FS

Mechanical parts

Material (wetted parts)	Stainless steel 316L or comparable
Pressure rating (PN)	up to 40 bar abs (PN10, 16, 40); for hazardous gases such as O ₂ , H ₂ , etc. do not exceed operating pressure of 10 bar; for higher pressure select a flanged type MFM, series F-107/F-117.
Process connections	Wafer type, for mounting between flanges according to DIN DN50 or ANSI 2"
Seals	standard: Viton®; options: EPDM, Kalrez® (FFKM)
Ingress protection	IP65

Electrical properties

Signal circuit	type of explosion protection: intrinsic safety Ex ib IIC, only for connection to a certified intrinsically safe circuit with the following maximum values: U _i = 28 V, I _i = 98 mA, P _i = 686 mW The effective internal capacitance between: Terminals 1 and 3: C _i = 1 nF; Effective internal inductance: L _i = 0,3 mH
Output signal	15 ... 20 mA (linear)
I/O signals via PS/Readout (located in safe area)	analog: 0...5 Vdc, 0...10 Vdc, 0...20 mA, 4...20 mA; digital: RS232, PROFIBUS DP, DeviceNet™, Modbus RTU or ASCII, PROFINET, EtherCAT®, FLOW- BUS

Electrical connection

Ex-proof measuring head	Terminal connection, cable gland M16x1,5
-------------------------	--

Technical specifications subject to change without notice.

For dimensional drawings and hook-up diagrams please visit the [product page](#) on our [website](#)

Recommended accessories




E-8000 SERIES

Digital Readout / Control Systems

Bright, wide angle, 1.8" display (TFT technology)

User friendly operation, menu driven with 4 push buttons

Related products



EX-FLOW F-106AX

Flow ranges from 0,4...20 m³n/h up to 4...200 m³n/h

Pressure rating up to 40 bar

ATEX approval Cat.2, Zone 1

Rugged IP65 construction



EX-FLOW F-116BX

Flow ranges from 1...50 m³n/h up to 7,5...375 m³n/h

Pressure rating 100 bar

ATEX approval Cat.2, Zone 1

Rugged IP65 construction




EX-FLOW F-107BX

Flow ranges from 1...50 m³n/h up to 10...500 m³n/h

Pressure rating up to 40 bar

ATEX approval Cat.2, Zone 1

Rugged IP65 construction



EX-FLOW F-106CX

Flow ranges from 2...100 m³n/h up to 20...1000 m³n/h

Pressure rating up to 40 bar

ATEX approval Cat.2, Zone 1

Rugged IP65 construction



BRONKHORST USA INC.

57 South Commerce Way

Suite 120

USA - Bethlehem, PA 18017

Tel. [+1-610-866-6750](tel:+1-610-866-6750)

sales@bronkhorstusa.com