

# F-106DX

---

## EX-FLOW F-106DX

Ex-Proof Mass Flow Meter for High Gas Flow

- ATEX approval Cat.2, Zone 1
- Also IECEx, TIIS and KCs certified
- High accuracy, excellent repeatability
- Virtually pressure and temperature independent
- "Wafer type" for mounting between flanges (DN100 / 4")



---

### Intrinsically Safe Gas Mass Flow Meters for high flow rates

Bronkhorst® EX-FLOW Mass Flow Meters (MFMs) are suited for precise gas flow measurement in ATEX Zone 1 hazardous areas. The MFM should be connected to a power supply with galvanic isolation / preamplifier / readout system (located in the safe zone). See Bronkhorst® [E-8000 Series](#).

EX-FLOW model F-106DX covers flow ranges from 3,6...180 m<sup>3</sup><sub>n</sub>/h up to 36...1800 m<sup>3</sup><sub>n</sub>/h (N<sub>2</sub>-equivalent) at operating pressures up to 40 bar.

The intrinsically safe measuring head of the flow meter is tested according to ATEX 114 Directive 2014/34/EU and approved under EC-Type Examination Number: KEMA 01ATEX1172, protection II 2 G Ex ib IIC T4 Gb.

Other certifications: IECEx (IECEx DEK14.0060), TIIS (検・第TC21584号) and KCs = Ex ib IIC T4.

## Technical specifications

### Measurement / control system

Flow range (intermediate ranges available)	min. 3,6...180 m <sup>3</sup> <sub>n</sub> /h max. 36...1800 m <sup>3</sup> <sub>n</sub> /h (based on N <sub>2</sub> )
Accuracy (incl. linearity) (based on actual calibration)	± 1 % FS up to 1100 m <sup>3</sup> <sub>n</sub> /h N <sub>2</sub> -equivalent; for higher flows please contact factory
Repeatability	< 0,2 % RD
Turndown ratio	1:50 (2...100%)
Time constant	5 sec.
Operating temperature	-10 ... +70 °C
Temperature sensitivity	zero: < 0,05% FS/°C; span: < 0,05% Rd/°C
Leak integrity, outboard	tested < 2 x 10 <sup>-9</sup> mbar l/s He
Attitude sensitivity	max. error at 90° off horizontal 0,2% FS at 1 bar, typical N <sub>2</sub>
Warm-up time	30 min. for optimum accuracy 2 min. for accuracy ± 2% FS

### Mechanical parts

Material (wetted parts)	Stainless steel 316L or comparable
Pressure rating (PN)	up to 40 bar abs (PN10, 16, 40); for hazardous gases such as O <sub>2</sub> , H <sub>2</sub> , etc. do not exceed operating pressure of 10 bar; for higher pressure select a flanged type MFM, series F-107/F-117.
Process connections	Wafer type, for mounting between flanges according to DIN DN100 or ANSI 4"
Seals	standard: Viton®; options: EPDM, Kalrez® (FFKM)
Ingress protection	IP65

### Electrical properties

Signal circuit	type of explosion protection: intrinsic safety Ex ib IIC, only for connection to a certified intrinsically safe circuit with the following maximum values: U <sub>i</sub> = 28 V, I <sub>i</sub> = 98 mA, P <sub>i</sub> = 686 mW The effective internal capacitance between: Terminals 1 and 3: C <sub>i</sub> = 1 nF; Effective internal inductance: L <sub>i</sub> = 0,3 mH
Output signal	15 ... 20 mA (linear)
I/O signals via PS/Readout (located in safe area)	analog: 0...5 Vdc, 0...10 Vdc, 0...20 mA, 4...20 mA; digital: RS232, PROFIBUS DP, DeviceNet™, Modbus RTU or ASCII, PROFINET, EtherCAT®, FLOW- BUS

### Electrical connection

Ex-proof measuring head	Terminal connection, cable gland M16x1,5
-------------------------	--

Technical specifications subject to change without notice.

For dimensional drawings and hook-up diagrams please visit the [product page](#) on our [website](#)

---

## Recommended accessories



### E-8000 SERIES

#### Digital Readout / Control Systems

Bright, wide angle, 1.8" display (TFT technology)

User friendly operation, menu driven with 4 push buttons

## Related products



**EX-FLOW F-106CX**

Flow ranges from 2...100 m<sup>3</sup>n/h up to 20...1000 m<sup>3</sup>n/h

Pressure rating up to 40 bar

ATEX approval Cat.2, Zone 1

Rugged IP65 construction



**EX-FLOW F-107DX**

Flow ranges from 3,6...180 m<sup>3</sup>n/h up to 36...1800 m<sup>3</sup>n/h

Pressure rating up to 40 bar

ATEX approval Cat.2, Zone 1

Rugged IP65 construction



**EX-FLOW F-106EX**

Flow ranges from 8...400 m<sup>3</sup>n/h up to 80...4000 m<sup>3</sup>n/h

Pressure rating up to 40 bar

ATEX approval Cat.2, Zone 1

Rugged IP65 construction



**BRONKHORST USA INC.**

57 South Commerce Way

Suite 120

USA - Bethlehem, PA 18017

Tel. +1-610-866-6750

[sales@bronkhorstusa.com](mailto:sales@bronkhorstusa.com)