

# F-111AX

---

## EX-FLOW F-111AX

Ex-Proof Mass Flow Meter for Gases

- ATEX approval Cat.2, Zone 1
- Also IECEx, TIIS and KCs certified
- High accuracy, excellent repeatability
- Virtually pressure and temperature independent
- Compact design



---

### Intrinsically Safe Gas Mass Flow Meters for low/medium flow rates

Bronkhorst® EX-FLOW Mass Flow Meters (MFMs) are suited for precise gas flow measurement in ATEX Zone 1 hazardous areas. The MFM should be connected to a power supply with galvanic isolation / preamplifier / readout system (located in the safe zone). See Bronkhorst® [E-8000 Series](#).

EX-FLOW model F-111AX covers flow ranges from 0,1...5 l<sub>n</sub>/min up to 2...100 l<sub>n</sub>/min (N<sub>2</sub>-equivalent) at operating pressures up to 100 bar.

The intrinsically safe measuring head of the flow meter is tested according to ATEX 114 Directive 2014/34/EU and approved under EC-Type Examination Number: KEMA 01ATEX1172, protection II 2 G Ex ib IIC T4 Gb.

Other certifications: IECEx (IECEx DEK14.0060), TIIS (検・第TC21584号) and KCs = Ex ib IIC T4.

## Technical specifications

### Measurement / control system

Flow range (intermediate ranges available)	min. 0,1...5 I <sub>N</sub> /min max. to 2...100 I <sub>N</sub> /min (based on N <sub>2</sub> )
Accuracy (incl. linearity) (based on actual calibration)	± 1 % FS
Repeatability	< 0,2 % RD
Turndown ratio	1:50 (2...100%)
Time constant	5 sec.
Operating temperature	-10 ... +70 °C
Temperature sensitivity	zero: < 0,05% FS/°C; span: < 0,05% Rd/°C
Leak integrity, outboard	tested < 2 x 10 <sup>-9</sup> mbar l/s He
Attitude sensitivity	max. error at 90° off horizontal 0,2% FS at 1 bar, typical N <sub>2</sub>
Warm-up time	30 min. for optimum accuracy 2 min. for accuracy ± 2% FS

### Mechanical parts

Material (wetted parts)	Stainless steel 316L or comparable
Pressure rating (PN)	100 bar abs
Process connections	compression type or face seal (VCR/VCO) couplings
Seals	standard: Viton®; options: EPDM, Kalrez® (FFKM), FDA and USP Class VI approved compounds
Ingress protection	IP65

### Electrical properties

Signal circuit	type of explosion protection: intrinsic safety Ex ib IIC, only for connection to a certified intrinsically safe circuit with the following maximum values: U <sub>i</sub> = 28 V, I <sub>i</sub> = 98 mA, P <sub>i</sub> = 686 mW The effective internal capacitance between: Terminals 1 and 3: C <sub>i</sub> = 1 nF; Effective internal inductance: L <sub>i</sub> = 0,3 mH
Output signal	15 ... 20 mA (linear)
I/O signals via PS/Readout (located in safe area)	analog: 0...5 Vdc, 0...10 Vdc, 0...20 mA, 4...20 mA; digital: RS232, PROFIBUS DP, DeviceNet™, Modbus RTU or ASCII, PROFINET, EtherCAT®, FLOW-BUS

### Electrical connection

Ex-proof measuring head	Terminal connection, cable gland M16x1,5
-------------------------	--

Technical specifications subject to change without notice.

For dimensional drawings and hook-up diagrams please visit the [product page](#) on our [website](#)

## Recommended accessories



### E-8000 SERIES

#### Digital Readout / Control Systems

Bright, wide angle, 1.8" display (TFT technology)

User friendly operation, menu driven with 4 push buttons



### IN-LINE FILTER SERIE M-411 RS

1/4" female in / male out

100 bar

Average porosity 0.5...15 µm

## Related products



### EX-FLOW F-111BX

Flow ranges from 0,3...15 mln/min up to 0,4...20 lln/min

Pressure rating 100 bar

ATEX approval Cat.2, Zone 1

Rugged IP65 construction



### EX-FLOW F-112AX

Flow ranges from 0,8...40 lln/min up to 5...250 lln/min

Pressure rating 100 bar

ATEX approval Cat.2, Zone 1

Rugged IP65 construction



### EX-FLOW F-201AX

Flow ranges from 0,1...5 lln/min up to 2...100 lln/min

Pressure rating 64 bar

ATEX approval Cat.2, Zone 1

Rugged IP65 construction



**BRONKHORST USA INC.**

57 South Commerce Way

Suite 120

USA - Bethlehem, PA 18017

Tel. [+1-610-866-6750](tel:+1-610-866-6750)

[sales@bronkhorstusa.com](mailto:sales@bronkhorstusa.com)