

F-121MX

EX-FLOW F-121MX

High-Pressure Mass Flow Meter for Gases, Ex-Protected Style

- ATEX approval Cat.2, Zone 1
- Also IECEx, TIIS and KCs certified
- High accuracy, excellent repeatability
- Virtually pressure and temperature independent
- Pressure rating 200 bar



Intrinsically Safe Gas Mass Flow Meters for low flow rates

Bronkhorst® EX-FLOW Mass Flow Meters (MFMs) are suited for precise gas flow measurement in ATEX Zone 1 hazardous areas. The MFM should be connected to a power supply with galvanic isolation / preamplifier / readout system (located in the safe zone). See Bronkhorst® [E-8000 Series](#).

EX-FLOW model F-121MX covers flow ranges from 0,3...15 ml_n/min up to 0,4...20 l_n/min (N₂-equivalent) at operating pressures up to 200 bar.

The intrinsically safe measuring head of the flow meter is tested according to ATEX 114 Directive 2014/34/EU and approved under EC-Type Examination Number: KEMA 01ATEX1172, protection II 2 G Ex ib IIC T4 Gb.

Other certifications: IECEx (IECEx DEK14.0060) and TIIS (検・第TC21584号).

Technical specifications

Measurement / control system

Flow range (intermediate ranges available)	min. 0,3...15 ml _n /min max. 0,4...20 l _n /min (based on N ₂)
Accuracy (incl. linearity) (based on actual calibration)	± 1 % FS
Repeatability	< 0,2 % RD
Turndown ratio	1:50 (2...100%)
Time constant	5 sec.
Operating temperature	-10 ... +70 °C
Temperature sensitivity	zero: < 0,05% FS/°C; span: < 0,05% Rd/°C
Leak integrity, outboard	tested < 2 x 10 ⁻⁹ mbar l/s He
Attitude sensitivity	max. error at 90° off horizontal 0,2% FS at 1 bar, typical N ₂
Warm-up time	30 min. for optimum accuracy 2 min. for accuracy ± 2% FS

Mechanical parts

Material (wetted parts)	Stainless steel 316L or comparable
Pressure rating (PN)	200 bar abs
Process connections	compression type or face seal (VCR/VCO) couplings
Seals	standard: Viton®; options: EPDM, Kalrez® (FFKM)
Ingress protection	IP65

Electrical properties

Signal circuit	type of explosion protection: intrinsic safety Ex ib IIC, only for connection to a certified intrinsically safe circuit with the following maximum values: U _i = 28 V, I _i = 98 mA, P _i = 686 mW The effective internal capacitance between: Terminals 1 and 3: C _i = 1 nF; Effective internal inductance: L _i = 0,3 mH
Output signal	15 ... 20 mA (linear)
I/O signals via PS/Readout (located in safe area)	analog: 0...5 Vdc, 0...10 Vdc, 0...20 mA, 4...20 mA; digital: RS232, PROFIBUS DP, DeviceNet™, Modbus RTU or ASCII, PROFINET, EtherCAT®, FLOW- BUS

Electrical connection

Ex-proof measuring head	Terminal connection, cable gland M16x1,5
-------------------------	--

Technical specifications subject to change without notice.

For dimensional drawings and hook-up diagrams please visit the [product page](#) on our [website](#)

Recommended accessories



E-8000 SERIES

Digital Readout / Control Systems

Bright, wide angle, 1.8" display (TFT technology)

User friendly operation, menu driven with 4 push buttons

Related products



EX-FLOW F-120MX

Lowest flow rates, from 0,15...7,5 mln/min
up to 0,18...9,5 mln/min

Pressure rating 200 bar

ATEX approval Cat.2, Zone 1

Rugged IP65 construction



EX-FLOW F-230MX

Min. flow 0,2...10 mln/min

Max. flow 10...500 mln/min

Pressure / ΔP up to 400 bar

ATEX approval Cat.2, Zone 1

Rugged IP65 construction



EX-FLOW F-122MX

Flow ranges from 0,3...15 ln/min up to
5...250 ln/min

Pressure rating 200 bar

ATEX approval Cat.2, Zone 1

Rugged IP65 construction



EX-FLOW F-232MX

Min. flow 0,2...10 ln/min

Max. flow 2...100 ln/min

Pressure / ΔP up to 400 bar

ATEX approval Cat.2, Zone 1

Rugged IP65 construction



BRONKHORST USA INC.

57 South Commerce Way

Suite 120

USA - Bethlehem, PA 18017

Tel. [+1-610-866-6750](tel:+1-610-866-6750)

sales@bronkhorstusa.com