

F-116AI

IN-FLOW 'HIGH-FLOW' F-116AI

Industrial Style Mass Flow Meter for High Gas Flow

- High accuracy, excellent repeatability
- Pressure rating 100 bar
- Virtually pressure and temperature independent
- Compact design
- Rugged, weatherproof housing (IP65, dust and waterproof)



Industrial Style Gas Mass Flow Meters for high flow rates

Bronkhorst® model F-116AI Mass Flow Meters (MFM) are suited for precise measurement of flow ranges between 0,3...15 m³_n/h and 4...200 m³_n/h at operating pressures up to 100 bar. The MFM consists of a thermal mass flow sensor and a microprocessor based pc-board with signal and fieldbus conversion and a PID controller for optional mass flow control by means of a separately mounted control valve. The IN-FLOW model is of rugged design (IP65) for use in industrial environments or even Zone 2 hazardous areas, with optional ATEX Cat. 3 or FM Class I, Div. 2 approval.

IN-FLOW series are equipped with a digital pc-board, offering high accuracy, excellent temperature stability and fast response. The main digital pc-board contains all of the general functions needed for measurement and control. In addition to the standard RS232 output the instruments also offer analog I/O. As an option, an on-board interface can be mounted to provide CANopen®, DeviceNet™, PROFIBUS DP, PROFINET, Modbus RTU/ASCII or FLOW-BUS protocols.

Technical specifications

Measurement / control system

| | |
|--|---|
| Flow range (intermediate ranges available) | min. 0,3...15 m ³ _n /h max. 4...200 m ³ _n /h (based on N ₂) |
| Accuracy (incl. linearity) (based on actual calibration) | ± 1 % FS |
| Repeatability | < 0,2 % RD |
| Turndown ratio | 1:50 |
| Multi fluid capability | Storage of max. 8 calibration curves |
| Response time (sensor) | typical: 0,5 sec. |
| Operating temperature | -10 ... +70 °C for ATEX cat. 3 and FM Class 1 Div 2 : 0...50°C |
| Temperature sensitivity | zero: < 0,05% FS/°C; span: < 0,05% Rd/°C |
| Pressure sensitivity | 0,1% Rd/bar typical N ₂ ; 0,01% Rd/bar typical H ₂ |
| Leak integrity, outboard | tested < 2 x 10 ⁻⁹ mbar l/s He |
| Attitude sensitivity | max. error at 90° off horizontal 0,2% FS at 1 bar, typical N ₂ |
| Warm-up time | 30 min. for optimum accuracy 2 min for accuracy ± 2% FS |

Mechanical parts

| | |
|-------------------------|--|
| Material (wetted parts) | stainless steel 316L or comparable |
| Pressure rating (PN) | 100 bar abs |
| Process connections | compression type or face seal couplings |
| Seals | standard: Viton®; options: EPDM, Kalrez® (FFKM) |
| Weight | 5,0 kg |
| Ingress protection | IP65 |

Electrical properties

| | | | | |
|-----------------------------------|--|----------------|----------------|--------------------|
| Power supply | +15 ... 24 Vdc | | | |
| Max. power consumption meter | Supply | at voltage I/O | at current I/O | extra for fieldbus |
| | 15 V | 95 mA | 125 mA | <75 mA |
| | 24 V | 65 mA | 85 mA | <50 mA |
| Max. Power consumption controller | Supply | at voltage I/O | at current I/O | extra for fieldbus |
| | 15 V | 290 mA | 320 mA | <75 mA |
| | 24 V | 200 mA | 215 mA | <50 mA |
| Analog output | 0...5 (10) Vdc or 0 (4)...20 mA (sourcing output) | | | |
| Digital communication | standard: RS232; options: CANopen®, DeviceNet™, PROFIBUS DP, PROFINET, Modbus RTU/ASCII or FLOW-BUS | | | |

Electrical connection

| | |
|---------------------------|---|
| Analog/RS232 | 8 DIN (male); |
| PROFIBUS DP | bus: 5-pin M12 (female); power: 8 DIN (male); |
| CANopen® / DeviceNet™ | 5-pin M12 (male); |
| FLOW-BUS/Modbus-RTU/ASCII | 5-pin M12 (male) |
| PROFINET | bus: 2 x 5-pin M12 (female) (in/out); power: 8 DIN (male); |
| IEC 61010-1 | IEC-61010-1:2010 including national deviations for UL (61010-1:2012) and CSA (C22.2 No. 61010-1-12) |

Technical specifications subject to change without notice.

For dimensional drawings and hook-up diagrams please visit the [product page](#) on our [website](#)

Recommended accessories



E-8000 SERIES

Digital Readout / Control Systems

Bright, wide angle, 1.8" display (TFT technology)
User friendly operation, menu driven with 4 push buttons



BRIGHT SERIES

Compact Local R/C Module

Bright, wide angle, 1.8" display
User friendly operation
Indication/operation/configuration



PIPS SERIES

Plug-in Power Supply

For lab-style or industrial devices
Interchangeable plugs (Euro, UK, USA, Australian, IEC) for mains connection

Related products



IN-FLOW F-113AI

Min. flow 4...200 l/min
Max. flow 8...1670 l/min
Pressure rating 100 bar
Compact IP65 design
High accuracy



IN-FLOW 'HIGH-FLOW' F-116BI

Min. flow 1 ... 50 m³n/h
Max. flow 7,5 ... 375 m³n/h
Pressure rating 100 bar
Compact IP65 design
High accuracy



IN-FLOW 'HIGH-FLOW' F-206BI

Min. flow 1 ... 50 m³n/h
Max. flow 7,5 ... 375 m³n/h
Pressure rating 64 bar
Compact IP65 design
High accuracy and repeatability



IN-FLOW 'HIGH-FLOW' F-216AI

Min. flow 0,3 ... 15 m³n/h
Max. flow 4 ... 200 m³n/h
Pressure rating 100 bar
Compact IP65 design
High accuracy and repeatability



BRONKHORST USA INC.

57 South Commerce Way

Suite 120

USA - Bethlehem, PA 18017

Tel. [+1-610-866-6750](tel:+1-610-866-6750)

sales@bronkhorstusa.com