

MV-192-H2

MASS-VIEW® MV-192-H2

Hydrogen Flow Meter with integrated display

- Direct thermal mass flow measurement
- High accuracy
- Bright, graphical OLED display
- Digital or analog output
- Alarm and counter functions

MASSFLOW-ONLINE PRODUCT



Hydrogen Mass Flow Meters with integrated display

MASS-VIEW® model MV-192-H2 Direct Thermal Mass Flow Meters (MFMs) are suited for precise measurement of flow ranges between 50...100 ml_n/min and 50...1000 ml_n/min hydrogen at operating pressures up to 10 bar(g). The MFM has an integrated graphical OLED display, clearly visible at wide angles, which allows reading of actual flow (value and a bar graph), total flow and type of gas.

The display features easy set up via a user-friendly menu, using a 4-way navigation push button. Features & functions include a variety of alarm and counter functions, an analog output signal, digital interfaces and two relay contacts.

The MASS-VIEW® series provides modern, novel and economical alternative to variable area meters (VA meters), also known as purge meters. Unlike conventional VA meters these new flow meters measure mass flow instead of volume flow.

Technical specifications

Measurement / control system

Flow range (intermediate ranges available)	min. 50...100 ml _n /min max. 50...1000 ml _n /min (based on N ₂)
Accuracy (incl. linearity) (based on actual calibration)	± 2% Rd for flow > 50% of max. capacity; ± (1% Rd + 0,5% FS) on lower flows
Repeatability	< 0,2 % FS typical
Turndown ratio	up to 1 : 20
Operating pressure	0 ... 10 bar(g) / 0 ... 150 psi(g)
Pressure coefficient	± 0,2% Rd/bar typical at Air
Standard calibration gas	Air, other gases are converted using our Fluidat® conversion model which will introduce extra inaccuracy
Response time (sensor)	0,3 sec.
Operating temperature	0 ... 50 °C (32 ... 122°F)
Temperature coefficient	Zero: <0,1% FS/°C, Span: <0,2% Rd/°C
Leak integrity, outboard	tested < 2 x 10 ⁻⁹ mbar l/s He
Attitude sensitivity	< 0,1 % FS

Mechanical parts

Material (wetted parts)	Aluminium
Test pressure	21 bar(a) / 300 psi(a)
Process connections	G 1/4" BSPP female thread (compression fittings optional)
Seals	Viton®
Weight	0,7 kg
Ingress protection	IP40

Electrical properties

Power supply	+15 ... 24 Vdc (+/- 10%)
Max. power consumption	approx. 135 mA
Analog output	0 ... 5 Vdc
Digital communication	RS232 / RS485 (Modbus RTU/ASCII)
Min. and max. relay contacts	switching current 0,5 A, 24 Vdc, one side grounded (0 Vdc power)
Electrical connection	8-pin RJ-45 modular jack

Technical specifications subject to change without notice.

For dimensional drawings and hook-up diagrams please visit the [product page](#) on our [website](#)

Related products



MASS-VIEW® MV-102

Min. flow 20...200 mln/min
Max. flow 20...2000 mln/min
Pressure rating 10 bar
Bright, graphical OLED display
10 pre-installed gases



MASS-VIEW® MV-392-H2

Min. flow 50...100 mln/min H2
Max. flow 50...1000 mln/min H2
Bright, graphical OLED display
High quality needle valve



MASS-VIEW® MV-191-H2

Min. flow 20...50 mln/min H2
Max. flow 20...200 mln/min H2
Pressure rating 10 bar
Bright, graphical OLED display
Electr. output, alarm and counter



MASS-VIEW® MV-194-H2

Min. flow 0,1...1 ln/min H2
Max. flow 0,1...10 ln/min H2
Bright, graphical OLED display
Electr. output, alarm and counter



BRONKHORST USA INC.

57 South Commerce Way

Suite 120

USA - Bethlehem, PA 18017

Tel. [+1-610-866-6750](tel:+1-610-866-6750)

sales@bronkhorstusa.com