

# ML120V00

---

## mini CORI-FLOW™ ML120V00

(Ultra) Low Flow Coriolis Mass Flow Meter

- High accuracy
- Fast response
- Independent of fluid properties
- Additional density and temperature output
- Compact, space saving design
- Very small internal volume



---

## Low Flow Coriolis Mass Flow Meters for Liquid and Gases

mini CORI-FLOW™ Mass Flow Meters and Controllers are precise and compact instruments, based on the [Coriolis measuring principle](#), designed to cover the needs of the low flow market. Bronkhorst® model ML120V00 Mass Flow Meter (MFM) is suited for highly accurate measurement of gas or liquid flow in the range of 0...200 g/h (which corresponds with 0...2,66 l<sub>n</sub>/min when used on nitrogen) at operating pressures up to 200 bar.

The flow meter offers “multi-range” functionality: factory calibrated ranges can be rescaled by the user, maintaining the original accuracy specs. The instrument contains a microprocessor based pc-board with signal and fieldbus conversion.

---

## Technical specifications

## Measurement / control system

Flow rates	Liquid: 0...200 g/h (nominal flow rate: 100 g/h); Gas: 0...2.66 l/min (N <sub>2</sub> ); Full Scale (FS) value is user-configurable
Mass flow accuracy	Liquid: ±0,2% of rate; Gas: ±0,5% of rate
Repeatability	± 0,05 % of rate ± ½(ZS* x 100/actual flow)%
Turndown ratio	up to 1:4000
Zero stability (ZS)	< ± 10 mg/h (Guaranteed at constant temperature and for unchanging process and environment conditions.)
Response time (sensor)	≤ 200 msec
Temperature effect	on zero: < 3 mg/h/°C; on span: < 0,005% Rd/°C; self heating (at zero flow): < 10°C (Depends on flow rate, heat capacity fluid, T amb., T fluid and cooling capacity.)
Operating temperature	0 ... 70 °C
Mounting	Any position, attitude sensitivity negligible. Instrument to be rigidly bolted to a stiff and heavy mass or construction for guaranteed zero stability. External shocks or vibrations should be avoided.
Temperature accuracy	± 0,5 °C
Density accuracy	< ± 5 kg/m <sup>3</sup>
Leak integrity, outboard	tested < 2 x 10 <sup>-9</sup> mbar l/s He
Warm-up time	> 30 min. for optimum accuracy

## Mechanical parts

Material (wetted parts)	stainless steel 316L or comparable
Pressure rating (PN)	200 bar abs
Process connections	compression type or face seal (VCR/VCO) couplings, or Tri-Clamp flanges (welded)
Seals	metal
Weight	0,8 kg
Ingress protection	IP40

## Electrical properties

Power supply	+15...24 Vdc +/- 10% Max. ripple recommended: 50 mV tt
Max. power consumption	max. 2,5 W
Analog output	0...5 (10) Vdc, min. load impedance > 2 kΩ; 0 (4)...20 mA (sourcing), max. load impedance < 375 Ω
Digital communication	standard: RS232; options: PROFIBUS DP, CANopen®, DeviceNet™, PROFINET, EtherCAT®, Modbus RTU, ASCII or TCP/IP, EtherNet/IP, POWERLINK, FLOW-BUS

## Electrical connection

Analog/RS232	9-pin D-connector (male);
PROFIBUS DP	bus: 9-pin D-connector (female); power: 9-pin D-connector (male);
CANopen® / DeviceNet™	5-pin M12-connector (male);
FLOW-BUS/Modbus-RTU/ASCII	RJ45 modular jack;
Modbus TCP / EtherNet/IP / POWERLINK	2 x RJ45 modular jack (in/out);
EtherCAT®/ PROFINET	2 x RJ45 modular jack (in/out);

Technical specifications subject to change without notice.

For dimensional drawings and hook-up diagrams please visit the [product page](#) on our [website](#)

## Recommended accessories



### E-8000 SERIES

#### Digital Readout / Control Systems

Bright, wide angle, 1.8" display (TFT technology)

User friendly operation, menu driven with 4 push buttons



### BRIGHT SERIES

#### Compact Local R/C Module

Bright, wide angle, 1.8" display

User friendly operation

Indication/operation/configuration



### PIPS SERIES

#### Plug-in Power Supply

For lab-style or industrial devices

Interchangeable plugs (Euro, UK, USA, Australian, IEC) for mains connection



## MOUNTING PARTS

#### Mass blocks and vibration dampeners

To guarantee zero stability of low flow Coriolis instruments

## Related products



**MINI CORI-FLOW™ ML120V21**

Flow range 0...200 g/h  
Pressure rating 5 bar  
Independent of fluid properties  
High accuracy, control



**MINI CORI-FLOW™ M12**

Flow range 0...200 g/h  
Pressure rating 200 bar  
Independent of fluid properties  
High accuracy, fast response



**MINI CORI-FLOW™ CORIOLIS WITH PUMP**

Min. flow 0,05...5 ml/h  
Max. flow 6...600 l/h  
Compact, integrated dosing solution  
Direct pump control



**BRONKHORST USA LLC**  
57 South Commerce Way  
Suite 120  
USA - Bethlehem, PA 18017  
Tel. [+1-610-866-6750](tel:+1-610-866-6750)  
[sales@bronkhorstusa.com](mailto:sales@bronkhorstusa.com)