

# DATASHEET F-107BX

---

## EX-FLOW F-107BX

Ex-Protected Mass Flow Meter for High Gas Flow



---

### Intrinsically Safe Gas Mass Flow Meters for high flow rates

Bronkhorst® EX-FLOW Mass Flow Meters (MFMs) are suited for precise gas flow measurement in ATEX Zone 1 hazardous areas. The MFM should be connected to a power supply with galvanic isolation / preamplifier / readout system (located in the safe zone). See Bronkhorst® [E-8000 Series](#).

EX-FLOW model F-107BX covers flow ranges from 1...50 m<sup>3</sup><sub>n</sub>/h up to 10...500 m<sup>3</sup><sub>n</sub>/h (N<sub>2</sub>-equivalent) at operating pressures up to 40 bar.

The intrinsically safe measuring head of the flow meter is tested according to ATEX 114 Directive 2014/34/EU and approved under EC-Type Examination Number: KEMA 01ATEX1172, protection II 2 G Ex ib IIC T4 Gb.

Other certifications: IECEx (IECEx DEK14.0060), TIIS (検・第TC21584号) and KCs = Ex ib IIC T4.

## Technical specifications

### Measurement / control system

Flow range (intermediate ranges available)	min. 1...50 m <sup>3</sup> <sub>n</sub> /h max. 10...500 m <sup>3</sup> <sub>n</sub> /h (based on N <sub>2</sub> )
Accuracy (incl. linearity) (based on actual calibration)	± 1 % FS
Repeatability	< 0,2 % RD
Turndown ratio	1:50 (2...100%)
Time constant	5 sec.
Operating temperature	-10 ... +70 °C
Temperature sensitivity	zero: < 0,05% FS/°C; span: < 0,05% Rd/°C
Leak integrity, outboard	tested < 2 x 10 <sup>-9</sup> mbar l/s He
Attitude sensitivity	max. error at 90° off horizontal 0,2% FS at 1 bar, typical N <sub>2</sub>
Warm-up time	30 min. for optimum accuracy 2 min. for accuracy ± 2% FS

### Mechanical parts

Material (wetted parts)	Stainless steel 316L or comparable
Pressure rating (PN)	40 bar abs
Process connections	Flanged type, according to DIN DN50 or ANSI 2"
Seals	standard: FKM/Viton®; options: EPDM, FFKM/Kalrez®
Ingress protection	IP65

### Electrical properties

Output signal	15 ... 20 mA (linear) Terminal connection, cable gland M16x1,5
I/O signals via PS/Readout (located in safe area)	analog: 0...5 Vdc, 0...10 Vdc, 0...20 mA, 4...20 mA; digital: RS232, PROFIBUS DP, DeviceNet™, Modbus RTU or ASCII, PROFINET, EtherCAT®, FLOW- BUS

### Electrical connection

Ex-proof measuring head	Terminal connection, cable gland M16x1,5
-------------------------	--

### Control valve options

### External actuator options to be connected to the controller

### Ex-proof specifications

### Approvals / certificates

Technical specifications subject to change without notice.

For dimensional drawings and hook-up diagrams please visit the [product page](#) on our [website](#)

---

## Recommended accessories



### E-8000 SERIES

#### Digital Readout / Control Systems

Bright, wide angle, 1.8" display (TFT technology)  
User friendly operation, menu driven with 4 push buttons

---

## Related products



**EX-FLOW F-107AX**

Flow ranges from 0,4... 20 m<sup>3</sup>n/h up to 4...200 m<sup>3</sup>n/h  
Pressure rating up to 40 bar  
ATEX approval Cat.2, Zone 1  
Rugged IP65 construction



**EX-FLOW F-106BX**

Flow ranges from 1...50 m<sup>3</sup>n/h up to 10...500 m<sup>3</sup>n/h  
Pressure rating up to 40 bar  
ATEX approval Cat.2, Zone 1  
Rugged IP65 construction



**EX-FLOW F-107CX**

Flow ranges from 2... 100 m<sup>3</sup>n/h up to 20... 1000 m<sup>3</sup>n/h  
Pressure rating up to 40 bar  
ATEX approval Cat.2, Zone 1  
Rugged IP65 construction

