

F-107DX

EX-FLOW F-107DX

Ex-Protected Mass Flow Meter for High Gas Flow

- ATEX approval Cat.2, Zone 1
- Also IECEx, TIIS and KCs certified
- High accuracy, excellent repeatability
- Virtually pressure and temperature independent
- Flanged connection (DIN DN100 or ANSI 4")



Intrinsically Safe Gas Mass Flow Meters for high flow rates

Bronkhorst® EX-FLOW Mass Flow Meters (MFMs) are suited for precise gas flow measurement in ATEX Zone 1 hazardous areas. The MFM should be connected to a power supply with galvanic isolation / preamplifier / readout system (located in the safe zone). See Bronkhorst® [E-8000 Series](#).

EX-FLOW model F-107DX covers flow ranges from 3,6...180 m³_n/h up to 36...1800 m³_n/h (N₂-equivalent) at operating pressures up to 40 bar.

The intrinsically safe measuring head of the flow meter is tested according to ATEX 114 Directive 2014/34/EU and approved under EC-Type Examination Number: KEMA 01ATEX1172, protection II 2 G Ex ib IIC T4 Gb.

Other certifications: IECEx (IECEx DEK14.0060), TIIS (検・第TC21584号) and KCs = Ex ib IIC T4.

Technical specifications

Measurement / control system

Flow range (intermediate ranges available)	min. 3,6...180 m ³ _n /h max. 36...1800 m ³ _n /h (based on N ₂)
Accuracy (incl. linearity) (based on actual calibration)	± 1 % FS up to 1100 m ³ _n /h N ₂ -equivalent; for higher flows please contact factory
Repeatability	< 0,2 % RD
Turndown ratio	1:50 (2...100%)
Time constant	5 sec.
Control stability	≤ ± 0,1 % FS typical
Operating temperature	-10 ... +70 °C
Temperature sensitivity	zero: < 0,05% FS/°C; span: < 0,05% Rd/°C
Leak integrity, outboard	tested < 2 x 10 ⁻⁹ mbar l/s He
Attitude sensitivity	max. error at 90° off horizontal 0,2% FS at 1 bar, typical N ₂
Warm-up time	30 min. for optimum accuracy 2 min. for accuracy ± 2% FS

Mechanical parts

Material (wetted parts)	Stainless steel 316L or comparable
Pressure rating (PN)	40 bar abs
Process connections	Flanged type, according to DIN DN100 or ANSI 4"
Seals	standard: Viton®; options: EPDM, Kalrez® (FFKM)
Ingress protection	IP65

Electrical properties

Output signal	15 ... 20 mA (linear) Terminal connection, cable gland M16x1,5
I/O signals via PS/Readout (located in safe area)	analog: 0...5 Vdc, 0...10 Vdc, 0...20 mA, 4...20 mA; digital: RS232, PROFIBUS DP, DeviceNet™, Modbus RTU or ASCII, PROFINET, EtherCAT®, FLOW- BUS

Electrical connection

Ex-proof measuring head	Terminal connection, cable gland M16x1,5
-------------------------	--

Technical specifications subject to change without notice.

For dimensional drawings and hook-up diagrams please visit the [product page](#) on our [website](#)

Recommended accessories



E-8000 SERIES

Digital Readout / Control Systems

Bright, wide angle, 1.8" display (TFT technology)

User friendly operation, menu driven with 4 push buttons

Related products



EX-FLOW F-107CX

Flow ranges from 2...100 m³n/h up to 20...1000 m³n/h

Pressure rating up to 40 bar

ATEX approval Cat.2, Zone 1

Rugged IP65 construction



EX-FLOW F-106DX

Flow ranges from 3,6...180 m³n/h up to 36...1800 m³n/h

Pressure rating up to 40 bar

ATEX approval Cat.2, Zone 1

Rugged IP65 construction



EX-FLOW F-106EX

Flow ranges from 8...400 m³n/h up to 80...4000 m³n/h

Pressure rating up to 40 bar

ATEX approval Cat.2, Zone 1

Rugged IP65 construction



BRONKHORST HIGH-TECH B.V.

Nijverheidsstraat 1A

NL-7261 AK Ruurlo (NL)

Tel. +31 573 45 88 00

info@bronkhorst.com