

# F-116AX

---

## EX-FLOW F-116AX

Ex-Protected Mass Flow Meter for High Gas Flow

- ATEX approval Cat.2, Zone 1
- Also IECEx, TIIS and KCs certified
- High accuracy, excellent repeatability
- Virtually pressure and temperature independent
- Compact design



---

### Intrinsically Safe Gas Mass Flow Meters for high flow rates

Bronkhorst® EX-FLOW Mass Flow Meters (MFMs) are suited for precise gas flow measurement in ATEX Zone 1 hazardous areas. The MFM should be connected to a power supply with galvanic isolation / preamplifier / readout system (located in the safe zone). See Bronkhorst® [E-8000 Series](#).

EX-FLOW model F-116AX covers flow ranges from 0,4...20 m<sup>3</sup><sub>n</sub>/h up to 4...200 m<sup>3</sup><sub>n</sub>/h (N<sub>2</sub>-equivalent) at operating pressures up to 100 bar.

The intrinsically safe measuring head of the flow meter is tested according to ATEX 114 Directive 2014/34/EU and approved under EC-Type Examination Number: KEMA 01ATEX1172, protection II 2 G Ex ib IIC T4 Gb.

Other certifications: IECEx (IECEx DEK14.0060), TIIS (検・第TC21584号) and KCs = Ex ib IIC T4.

---

## Technical specifications

### Measurement / control system

Flow range (intermediate ranges available)	min. 0,4...20 m <sup>3</sup> <sub>n</sub> /h max. 4...200 m <sup>3</sup> <sub>n</sub> /h (based on N <sub>2</sub> )
Accuracy (incl. linearity) (based on actual calibration)	± 1 % FS
Repeatability	< 0,2 % RD
Turndown ratio	1:50 (2...100%)
Time constant	5 sec.
Operating temperature	-10 ... +70 °C
Temperature sensitivity	zero: < 0,05% FS/°C; span: < 0,05% Rd/°C
Leak integrity, outboard	tested < 2 x 10 <sup>-9</sup> mbar l/s He
Attitude sensitivity	max. error at 90° off horizontal 0,2% FS at 1 bar, typical N <sub>2</sub>
Warm-up time	30 min. for optimum accuracy 2 min. for accuracy ± 2% FS

### Mechanical parts

Material (wetted parts)	Stainless steel 316L or comparable
Pressure rating (PN)	100 bar abs
Process connections	compression type or face seal (VCR/VCO) couplings
Seals	standard: Viton®; options: EPDM, Kalrez® (FFKM)
Ingress protection	IP65

### Electrical properties

Output signal	15 ... 20 mA (linear) Terminal connection, cable gland M16x1,5
I/O signals via PS/Readout (located in safe area)	analog: 0...5 Vdc, 0...10 Vdc, 0...20 mA, 4...20 mA; digital: RS232, PROFIBUS DP, DeviceNet™, Modbus RTU or ASCII, PROFINET, EtherCAT®, FLOW- BUS

### Electrical connection

Ex-proof measuring head	Terminal connection, cable gland M16x1,5
-------------------------	--

Technical specifications subject to change without notice.

For dimensional drawings and hook-up diagrams please visit the [product page](#) on our [website](#)

---

## Recommended accessories



### E-8000 SERIES

#### Digital Readout / Control Systems

Bright, wide angle, 1.8" display (TFT technology)

User friendly operation, menu driven with 4 push buttons

---

## Related products



**EX-FLOW F-113AX**

Flow ranges from 4...200 l/min up to  
25...1250 l/min  
Pressure rating 100 bar  
ATEX approval Cat.2, Zone 1  
Rugged IP65 construction



**EX-FLOW F-116BX**

Flow ranges from 1...50 m<sup>3</sup>/h up to  
7,5...375 m<sup>3</sup>/h  
Pressure rating 100 bar  
ATEX approval Cat.2, Zone 1  
Rugged IP65 construction



**EX-FLOW F-106AX**

Flow ranges from 0,4...20 m<sup>3</sup>/h up to  
4...200 m<sup>3</sup>/h  
Pressure rating up to 40 bar  
ATEX approval Cat.2, Zone 1  
Rugged IP65 construction



**EX-FLOW F-107AX**

Flow ranges from 0,4...20 m<sup>3</sup>/h up to  
4...200 m<sup>3</sup>/h  
Pressure rating up to 40 bar  
ATEX approval Cat.2, Zone 1  
Rugged IP65 construction



**BRONKHORST HIGH-TECH B.V.**

Nijverheidsstraat 1A

NL-7261 AK Ruurlo (NL)

Tel. +31 573 45 88 00

[info@bronkhorst.com](mailto:info@bronkhorst.com)