

F-213AX

EX-FLOW F-213AX

Ex-Protected Mass Flow Controller for Gases

- ATEX approval Cat.2, Zone 1
- High accuracy, excellent repeatability
- Virtually pressure and temperature independent
- Compact design



Intrinsically Safe Gas Mass Flow Controllers for higher flow rates

Bronkhorst® EX-FLOW Mass Flow Controllers (MFCs) are suited for precise gas flow control in ATEX Zone 1 hazardous areas. The flow meter part and the control valve of the MFC should be connected (via separate cables) to a power supply with galvanic isolation / preamplifier / readout system (located in the safe zone) which contains a controller board to complete the control loop. See Bronkhorst® [E-8000 Series](#).

EX-FLOW model F-213AX covers flow ranges from 4...200 l_n/min up to 25...1250 l_n/min (N₂-equivalent) at operating pressures up to 100 bar.

The intrinsically safe measuring head of the flow meter is tested according to ATEX 114 Directive 2014/34/EU and approved under EC-Type Examination Number: KEMA 01ATEX1172, protection II 2 G Ex ib IIC T4 Gb.

The intrinsically safe valve coils are explosion proof certified and available in two options (ATEX certification only):

Coil XB: protection II 1 G Ex ia IIC T6 / protection II 1 D Ex ta IIIC T80°C

Coil XC: protection II 2 G Ex eb IIC T4 / protection II 2 D Ex tb IIIC T130°C

Technical specifications

Measurement / control system

Flow range (intermediate ranges available)	min. 4...200 I _n /min max. 25...1250 I _n /min (based on N ₂)
Accuracy (incl. linearity) (based on actual calibration)	± 1 % FS
Repeatability	< 0,2 % RD
Turndown ratio	1:50 (2...100%)
Time constant	5 sec.
Control stability	≤ ± 0,1 % FS typical
Operating temperature	-10 ... +65 °C
Temperature sensitivity	zero: < 0,05% FS/°C; span: < 0,05% Rd/°C
Max. Kv-value	0,15 ... 1,5
Leak integrity, outboard	tested < 2 x 10 ⁻⁹ mbar l/s He
Attitude sensitivity	max. error at 90° off horizontal 0,2% FS at 1 bar, typical N ₂
Warm-up time	30 min. for optimum accuracy 2 min. for accuracy ± 2% FS

Mechanical parts

Material (wetted parts)	Stainless steel 316L or comparable
Pressure rating (PN)	100 bar abs
Process connections	compression type or face seal (VCR/VCO) couplings
Seals	standard: Viton®; options: EPDM, Kalrez® (FFKM), FDA and USP Class VI approved compounds
Ingress protection	IP65

Electrical properties

Output signal	15 ... 20 mA (linear) Terminal connection, cable gland M16x1,5
I/O signals via PS/Readout (located in safe area)	analog: 0...5 Vdc, 0...10 Vdc, 0...20 mA, 4...20 mA; digital: RS232, PROFIBUS DP, DeviceNet™, Modbus RTU or ASCII, PROFINET, EtherCAT®, FLOW- BUS
XB-coil	Coil voltage max. 28 V/110 mA; 295 Ohm at 20°C
XC-coil	Coil voltage max. 24 V; 65 Ohm at 20°C, Pmax = 9 W at 20°C

Electrical connection

Ex-proof measuring head	Terminal connection, cable gland M16x1,5
Control valve coil	cable gland M20x1,5

Technical specifications subject to change without notice.

For dimensional drawings and hook-up diagrams please visit the [product page](#) on our [website](#)

Recommended accessories



E-8000 SERIES

Digital Readout / Control Systems

Bright, wide angle, 1.8" display (TFT technology)

User friendly operation, menu driven with 4 push buttons



IN-LINE FILTER SERIE M-423 RS

1/2" female in / male out

200 bar

Average porosity 2...40 µm

Related products



EX-FLOW F-212AX

Flow ranges from 0,6...30 l/min up to
5...250 l/min
Pressure rating 100 bar
ATEX approval Cat.2, Zone 1
Rugged IP65 construction



EX-FLOW F-113AX

Flow ranges from 4...200 l/min up to
25...1250 l/min
Pressure rating 100 bar
ATEX approval Cat.2, Zone 1
Rugged IP65 construction



EX-FLOW F-216AX

Flow ranges from 0,4...20 m³/h up to
4...200 m³/h
Pressure rating 100 bar
ATEX approval Cat.2, Zone 1
Rugged IP65 construction



BRONKHORST HIGH-TECH B.V.

Nijverheidsstraat 1A
NL-7261 AK Ruurlo (NL)
Tel. [+31 573 45 88 00](tel:+31573458800)
info@bronkhorst.com