

# DATASHEET F-206AI

## IN-FLOW High-Flow F-206AI

Industrial Style Mass Flow Controller for High Gas Flow



### Industrial Style Gas Mass Flow Controllers for high flow rates

Bronkhorst® model F-206AI Mass Flow Controllers (MFCs) are suited for accurate measurement and control of flow ranges between 0,3...15 m<sup>3</sup><sub>n</sub>/h and 4...200 m<sup>3</sup><sub>n</sub>/h with operating pressures up to 64 bar. The MFC consists of a thermal mass flow sensor, a precise control valve and a microprocessor based pc-board with signal and fieldbus conversion. As a function of a setpoint value, the flow controller swiftly adjusts the desired flow rate. The IN-FLOW model is of rugged design (IP65) for use in industrial environments or even Zone 2 hazardous areas, with optional ATEX Cat. 3 or FM Class I, Div. 2 approval.

IN-FLOW series are equipped with a digital pc-board, offering high accuracy, excellent temperature stability and fast response. The main digital pc-board contains all of the general functions needed for measurement and control. In addition to the standard RS232 output the instruments also offer analog I/O. As an option, an on-board interface can be mounted to provide CANopen®, DeviceNet™, EtherCAT®, PROFIBUS DP, PROFINET, Modbus RTU, ASCII or TCP/IP, EtherNet/IP, POWERLINK or FLOW-BUS protocols.

### Technical specifications

#### Measurement / control system

Flow range (intermediate ranges available)	min. 0,3...15 m <sup>3</sup> <sub>n</sub> /h max. 4...200 m <sup>3</sup> <sub>n</sub> /h (based on N <sub>2</sub> )
Accuracy (incl. linearity) (based on actual calibration)	± 1 % FS
Repeatability	< 0,2 % RD
Turndown ratio	1:50
Multi fluid capability	Storage of max. 8 calibration curves
Settling time (in control, typical)	2 ... 4 sec.
Control stability	< ± 0,1 % FS
Operating temperature	-10 ... +70 °C for ATEX cat. 3 and FM Class 1 Div 2 : 0...50°C
Temperature sensitivity	zero: < 0,05% FS/°C; span: < 0,05% Rd/°C
Pressure sensitivity	0,1% Rd/bar typical N <sub>2</sub> ; 0,01% Rd/bar typical H <sub>2</sub>
Max. Kv-value	0,15 ... 1,5
Leak integrity, outboard	tested < 2 x 10 <sup>-9</sup> mbar l/s He
Attitude sensitivity	max. error at 90° off horizontal 0,2% at 1 bar, typical N <sub>2</sub>

## Measurement / control system

Warm-up time	30 min. for optimum accuracy 2 min for accuracy $\pm 2\%$ FS
--------------	---

## Mechanical parts

Material (wetted parts)	stainless steel 316L or comparable
Pressure rating (PN)	64 bar abs
Max. $\Delta P$	20 bar(d)
Process connections	compression type or face seal couplings
Seals	standard: FKM/Viton®; options: EPDM, FFKM/Kalrez®
Weight	6,7 kg
Ingress protection	IP65

## Electrical properties

Power supply	+15 ... 24 Vdc			
Max. power consumption	Supply	at voltage I/O	at current I/O	extra for fieldbus
	15 V	290 mA	320 mA	<75 mA
	24 V	200 mA	215 mA	<50 mA
Analog output	0...5 (10) Vdc or 0 (4)...20 mA (sourcing output)			
Digital communication	standard: RS232; options: CANopen®, DeviceNet™, EtherCAT®, PROFIBUS DP, PROFINET, Modbus RTU, ASCII or TCP/IP, EtherNet/IP, POWERLINK or FLOW-BUS			

## Electrical connection

Analog/RS232	8 DIN (male);
PROFIBUS DP	bus: 5-pin M12 (female); power: 8 DIN (male);
CANopen® / DeviceNet™	5-pin M12 (male);
FLOW-BUS/Modbus-RTU/ASCII	5-pin M12 (male)
Modbus TCP / EtherNet/IP / POWERLINK	bus: 2 x 5-pin M12 (female) (in/out); power: 8 DIN (male);
EtherCAT® / PROFINET	bus: 2 x 5-pin M12 (female) (in/out); power: 8 DIN (male)
IEC 61010-1	IEC-61010-1:2010 including national deviations for UL (61010-1:2012) and CSA (C22.2 No. 61010-1-12)

## Control valve options

## External actuator options to be connected to the controller

## Certification for hazardous areas

## Approvals / certificates

Technical specifications subject to change without notice.

For dimensional drawings and hook-up diagrams please visit the [product page](#) on our [website](#)

## Recommended accessories



**E-8000 SERIES**

### Digital Readout / Control Systems

Bright, wide angle, 1.8" display (TFT technology)  
User friendly operation, menu driven with 4 push buttons



**BRIGHT SERIES**

### Compact Local R/C Module

Bright, wide angle, 1.8" display  
User friendly operation  
Indication/operation/configuration



**PIPS SERIES**

### Plug-in Power Supply

For lab-style or industrial devices  
Interchangeable plugs (Euro, UK, USA, Australian, IEC) for mains connection

## Related products



**IN-FLOW F-203AI**

Min. flow 4...200 l/min  
Max. flow 33...1670 l/min  
Pressure rating 64 bar  
Compact IP65 design  
High accuracy and repeatability



**IN-FLOW HIGH-FLOW F-206BI**

Min. flow 1 ... 50 m<sup>3</sup>/h  
Max. flow 7,5 ... 375 m<sup>3</sup>/h  
Pressure rating 64 bar  
Compact IP65 design  
High accuracy and repeatability



**IN-FLOW HIGH-FLOW F-116AI**

Min. flow 0,3 ... 15 m<sup>3</sup>/h  
Max. flow 4 ... 200 m<sup>3</sup>/h  
Pressure rating 100 bar  
Compact IP65 design  
High accuracy

