

MV-391-HE

MASS-VIEW® MV-391-HE

Helium Flow Regulator with integrated display

- Direct thermal mass flow measurement
- High accuracy
- Bright, graphical OLED display
- Digital or analog output; alarm and counter functions
- High precision needle valve

MASSFLOW-ONLINE PRODUCT



Helium Mass Flow Regulators with integrated display

MASS-VIEW® model MV-391-HE Mass Flow Regulators (MFRs) are suited for precise measurement and control of flow ranges between 20...50 ml_n/min and 20...200 ml_n/min helium at operating pressures up to 10 bar(g). The MFR has an integrated graphical OLED display, clearly visible at wide angles, which allows reading of actual flow (value and a bar graph), total flow and type of gas. A high quality needle valve offers smooth and fine adjustment of the gas flow.

The display features easy set up via a user-friendly menu, using a 4-way navigation push button. Features & functions include a variety of alarm and counter functions, an analog output signal, digital interfaces and two relay contacts.

The MASS-VIEW® series provides modern, novel and economical alternative to variable area meters (VA meters), also known as purge meters. Unlike conventional VA meters these new flow meters measure mass flow instead of volume flow.

Technical specifications

Measurement system

Flow range, based on Helium (intermediate ranges available)	min. 20...50 ml _n /min max. 20...200 ml _n /min
Accuracy	± 2% Rd for flow > 50% of max. capacity; ± (1% Rd + 0,5% FS) on lower flows
Repeatability	< 0,2% FS typical
Standard calibration gas	Air, other gases are converted using our Fluidat [®] conversion model which will introduce extra inaccuracy
Turndown	up to 1 : 10
Operating pressure	0 ... 10 bar(g) / 0 ... 150 psi(g)
Pressure coefficient	± 0,2% Rd/bar typical at Air
Operating temperature	0 ... 50°C (32 ... 122°F)
Temperature coefficient	Zero: <0,1% FS/°C, Span: <0,2% Rd/°C
Response time sensor (t63%)	0,3 sec.
Leak integrity	tested < 2 x 10 ⁻⁹ mbar l/s He
Attitude sensitivity	< 0,1% FS

Mechanical parts

Material (wetted parts)	Meter: Aluminium; Needle valve: SS316
Test pressure	21 bar(a) / 300 psi(a)
Process connections	G 1/4" BSPP female thread (compression fittings optional)
Seals	Viton [®] , PTFE
Weight	0,7 kg
Ingress protection	IP40

Electrical specifications

Power supply	+15...24 Vdc (+/- 10%)
Power consumption	approx.135 mA
Min. and max. relay contacts	switching current 0,5 A, 24 Vdc, one side grounded (0 Vdc power)
Analog output	0...5 Vdc
Digital communication	RS232 / RS485 (Modbus RTU/ASCII)
Electrical connection	8-pin RJ-45 modular jack

- Technical specifications subject to change without notice.

For dimensional drawings and hook-up diagrams please visit the [productpage](#) on our [website](#)

Related products



MASS-VIEW® MV-301

Min. flow 10...50 mln/min
Max. flow 10...200 mln/min
Pressure rating 10 bar
Bright, graphical OLED display
High quality needle valve



MASS-VIEW® MV-191-HE

Min. flow 20...50 mln/min He
Max. flow 20...200 mln/min He
Bright, graphical OLED display
Electr. output, alarm and counter



MASS-VIEW® MV-392-HE

Min. flow 50...200 mln/min He
Max. flow 50...2000 mln/min He
Bright, graphical OLED display
High quality needle valve



BRONKHORST HIGH-TECH B.V.

Nijverheidsstraat 1A
NL-7261 AK Ruurlo (NL)
Tel. [+31 573 45 88 00](tel:+31573458800)
info@bronkhorst.com