

# DATASHEET P-512C

## EL-PRESS P-512C

Digital Electronic Pressure Meter



### Digital Electronic Pressure Meters

Bronkhorst® model P-512C Electronic Pressure Transducers (EPTs) are suited for precise measurement of pressure ranges between 1,28...64 bar and 2...100 bar absolute or gauge. The EPT has a well-proven compact thru-flow design and includes a diaphragm type piezo-resistive pressure sensor, a microprocessor based pc-board with signal and fieldbus conversion and a PID controller for optional pressure control by means of a separately mounted control valve.

EL-PRESS series are equipped with a digital pc-board, offering high accuracy, excellent temperature stability and fast response. The main digital pc-board contains all of the general functions needed for measurement and control. In addition to the standard RS232 output the instruments also offer analog I/O. As an option, an on-board interface can be mounted to provide CANopen®, DeviceNet™, EtherCAT®, PROFIBUS DP, PROFINET, Modbus RTU, ASCII or TCP/IP, EtherNet/IP, POWERLINK or FLOW-BUS protocols.

### Technical specifications

#### Measurement / control system

Absolute pressure sensors	Code: M10A - Ranges (FS): 20 ... 100 bara - P-max: 200 bara Code: M40A - Ranges (FS): 100 ... 400 bara - P-max: 500 bara
Accuracy (incl. linearity and hysteresis)	standard: $\pm 0,5\%$ FS
Repeatability	$< 0,1\%$ RD
Pressure rangeability	1:50 for pressure meter; 1 : 20 for P2-control; 1 : 5 for P1-control
Response time (sensor)	2 msec
Operating temperature	-10 ... +70 °C
Temperature sensitivity	0,1% FS/°C
Leak integrity, outboard	tested $< 2 \times 10^{-9}$ mbar l/s He
Attitude sensitivity	max. error at 90° off horizontal $< 0,3$ mbar
Warm-up time	negligible

#### Mechanical parts

Material (wetted parts)	stainless steel 316L or comparable
Process connections	compression type or face seal (VCR/VCO) couplings
Seals	standard: Viton®; options: EPDM, Kalrez® (FFKM), FDA and USP Class VI approved compounds
Weight	0,4 kg

Mechanical parts

Ingress protection	IP40
--------------------	------

Electrical properties

Power supply	+15 ... 24 Vdc			
Max. power consumption meter	Supply	at voltage I/O	at current I/O	extra for fieldbus
	15 V	95 mA	125 mA	<75 mA
	24 V	65 mA	85 mA	<50 mA
Max. Power consumption controller	Supply	at voltage I/O	at current I/O	extra for fieldbus
	15 V	290 mA	320 mA	<75 mA
	24 V	200 mA	215 mA	<50 mA
Analog output	0...5 (10) Vdc or 0 (4)...20 mA (sourcing output)			
Digital communication	standard: RS232; options: CANopen®, DeviceNet™, EtherCAT®, PROFIBUS DP, PROFINET, Modbus RTU, ASCII or TCP/IP, EtherNet/IP, POWERLINK or FLOW-BUS			

Electrical connection

Analog/RS232	9-pin D-connector (male);
PROFIBUS DP	bus: 9-pin D-connector (female); power: 9-pin D-connector (male);
CANopen® / DeviceNet™	5-pin M12-connector (male);
FLOW-BUS/Modbus-RTU/ASCII	RJ45 modular jack
Modbus TCP / EtherNet/IP / POWERLINK	2 x RJ45 modular jack (in/out);
EtherCAT® / PROFINET	2 x RJ45 modular jack (in/out);

Control valve options

External actuator options to be connected to the controller

Ex-proof specifications

Approvals / certificates

Technical specifications subject to change without notice.

**Note:** The measuring cell of the pressure sensor is separated from the external pressure by a thin, sensitive stainless steel diaphragm, and the sealed off cavity between diaphragm and cell is filled with oil. Since the standard oil filling is flammable, Bronkhorst advises to take precautions when oxygen or any other explosive fluid is used.

For dimensional drawings and hook-up diagrams please visit the [product page](#) on our [website](#)

Recommended accessories



E-8000 SERIES

Digital Readout / Control Systems

Bright, wide angle, 1.8" display (TFT technology)  
User friendly operation, menu driven with 4 push buttons



BRIGHT SERIES

Compact Local R/C Module

Bright, wide angle, 1.8" display  
User friendly operation  
Indication/operation/configuration



PIPS SERIES

Plug-in Power Supply

For lab-style or industrial devices  
Interchangeable plugs (Euro, UK, USA, Australian, IEC) for mains connection

Related products



EL-PRESS P-502C

Min. pressure 2...100 mbar  
Max. pressure 1,28...64 bar  
Absolute or gauge pressure  
High accuracy



EL-PRESS P-612CV (P2-CONTROL)

Min. pressure 3,2...64 bar  
Max. pressure 5...100 bar  
Absolute or gauge pressure  
High accuracy



EL-PRESS P-712CV (P1-CONTROL)

Min. pressure 12,8...64 bar  
Max. pressure 20...100 bar  
Absolute or gauge pressure  
High accuracy



EL-PRESS P-522C

Min. pressure 2...100 bar  
Max. pressure 4...200 bar  
Absolute or gauge pressure  
High accuracy



**BRONKHORST HIGH-TECH B.V.**

Nijverheidsstraat 1A

NL-7261 AK Ruurlo (NL)

Tel. +31 573 45 88 00

[info@bronkhorst.com](mailto:info@bronkhorst.com)

