

DATASHEET P-802CI

IN-PRESS P-802CI

Process Pressure Controller, Industrial Style



Process Pressure Controller, Industrial Style

Bronkhorst® model P-802CI Process Pressure Controllers (PPCs) are suited for precise pressure control with closed volumes, i.e. with one fluid connection. This PPC model is suited for pressure ranges between 17,5...350 mbar and 3,2...64 bar absolute or gauge. The instrument comprises a diaphragm type piezo-resistive pressure sensor, a microprocessor based pc-board with signal and fieldbus conversion and a PID controller for pressure control by means of two integrated control valves. This dual valve construction is a compact, economical alternative to configurations where forward pressure controllers are combined with separate bleed ports and relief valves. It is considered as a great advantage that the relief valve does not vent to the atmosphere. Furthermore the system can be set for either fast or smooth controlled (de)pressurization. The IN-PRESS model is of rugged design (IP65) for use in industrial environments.

IN-PRESS series are equipped with a digital pc-board, offering high accuracy, excellent temperature stability and fast response. The main digital pc-board contains all of the general functions needed for measurement and control. In addition to the standard RS232 output the instruments also offer analog I/O. As an option, an on-board interface can be mounted to provide CANopen®, DeviceNet™, EtherCAT®, PROFIBUS DP, PROFINET, Modbus RTU, ASCII or TCP/IP, EtherNet/IP, POWERLINK or FLOW-BUS protocols.

Technical specifications

Measurement / control system

Pressure ranges	min. 17,5 ... 350 mbar max. 3,2 ... 64 bar
Accuracy (incl. linearity and hysteresis)	± 0,5 % FS
Repeatability	< 0,25 % RD
Pressure rangeability	1:20 (with flow range 1:50)
Response time (sensor)	2 msec
Operating temperature	-10 ... +70 °C
Temperature sensitivity	0,1% FS/°C
Leak integrity, outboard	tested < 2 x 10 ⁻⁹ mbar l/s He
Attitude sensitivity	max. error at 90° off horizontal < 0,3 mbar
Warm-up time	negligible

Mechanical parts

Material (wetted parts)	stainless steel 316L or comparable
Process connections	compression type or face seal (VCR/VCO) couplings

Mechanical parts

Seals	standard: FKM/Viton®; options: EPDM, FFKM/Kalrez®, FDA and USP Class VI approved compounds
Weight	2,8 kg
Ingress protection	IP65

Electrical properties

Power supply	+15 ... 24 Vdc			
Max. power consumption	Supply	at voltage I/O	at current I/O	extra for fieldbus
	15 V	290 mA	320 mA	<75 mA
	24 V	200 mA	215 mA	<50 mA
PROFIBUS DP	add 53 mA (15 V supply) or 30 mA (24 V supply)			
CANopen® / DeviceNet™	add 48 mA (24 V supply)			
Analog output	0...5 (10) Vdc or 0 (4)...20 mA (sourcing output)			
Digital communication	standard: RS232; options: CANopen®, DeviceNet™, EtherCAT®, PROFIBUS DP, PROFINET, Modbus RTU, ASCII or TCP/IP, EtherNet/IP, POWERLINK or FLOW-BUS			

Electrical connection

Analog/RS232	8 DIN (male);
PROFIBUS DP	bus: 5-pin M12 (female); power: 8 DIN (male);
CANopen® / DeviceNet™	5-pin M12-connector (male);
FLOW-BUS/Modbus-RTU/ASCII	5-pin M12 (male)
Modbus TCP / EtherNet/IP / POWERLINK	bus: 2 x 5-pin M12 (female) (in/out); power: 8 DIN (male);
EtherCAT®/ PROFINET	bus: 2 x 5-pin M12 (female) (in/out); power: 8 DIN (male)

Control valve options

External actuator options to be connected to the controller

Ex-proof specifications

Approvals / certificates

Technical specifications subject to change without notice.

Note: The measuring cell of the pressure sensor is separated from the external pressure by a thin, sensitive stainless steel diaphragm, and the sealed off cavity between diaphragm and cell is filled with oil. Since the standard oil filling is flammable, Bronkhorst advises to take precautions when oxygen or any other explosive fluid is used.

For dimensional drawings and hook-up diagrams please visit the [product page](#) on our [website](#)

Recommended accessories



E-8000 SERIES

Digital Readout / Control Systems

Bright, wide angle, 1.8" display (TFT technology)
User friendly operation, menu driven with 4 push buttons



BRIGHT SERIES

Compact Local R/C Module

Bright, wide angle, 1.8" display
User friendly operation
Indication/operation/configuration



PIPS SERIES

Plug-in Power Supply

For lab-style or industrial devices
Interchangeable plugs (Euro, UK, USA, Australian, IEC) for mains connection

Related products



IN-PRESS P-812CI

Min. pressure 3,2...64 bar
Max. pressure 5...100 bar
Absolute or gauge pressure
Fast or smooth pressure control
Rugged IP65 construction



IN-PRESS P-822CI

Min. pressure 5...100 bar
Max. pressure 10...200 bar
Absolute or gauge pressure
Fast or smooth pressure control
Rugged IP65 construction



EL-PRESS P-802CV

Min. pressure 17,5...350 mbar
Max. pressure 3,2...64 bar
Absolute or gauge pressure
Fast or smooth pressure control

