

# W-202A

---

## CEM EVAPORATOR W-202A

### 3-Way Mixing Valve and Evaporator

- Accurately controlled gas/liquid mixture
- Fast response
- High reproducibility
- Very stable vapour flow



---

### 3-way Mixing Valve and Evaporator

Bronkhorst® model W-202A CEM 3-way Mixing Valve and Evaporator is suited for precise vapour flow delivery, composed by mixing up to 120 g/h H<sub>2</sub>O (320 g/h IPA) with max. 10 l<sub>n</sub>/min of carrier gas at operating pressures between vacuum and 100 bar. The temperature controlled mixing device is used in combination with a (thermal or Coriolis) liquid flow meter and an MFC for carrier gas, together forming a Controlled Evaporation and Mixing (CEM) System.

---

## Technical specifications

### Measurement / control system

Max. heating temperature	200 °C
--------------------------	--------

Heater capacity	100 W
-----------------	-------

Max. Kv-value	$6,6 \times 10^{-2}$
---------------	----------------------

### Mechanical parts

Material (wetted parts)	Stainless steel 316L or comparable
-------------------------	------------------------------------

Pressure rating (PN)	100 bar a
----------------------	-----------

Max. $\Delta P$	5 ... 40 bar (depends on Kv-value; contact your distributor for details)
-----------------	---

Process connections	Gas and liquid inlet: compression type or face seal couplings; Vapour outlet: 1/8" tube (other options on request); Purge connection: 1/8" OD or 1/8" face seal
---------------------	---

Seals	Metal-to-metal
-------	----------------

Protection class	IP40
------------------	------

Plunger	Kalrez®; other on request
---------	---------------------------

Connector	Amphenol 6-pin male
-----------	---------------------

### Electrical properties

Power supply	Mixing valve: +15...24 Vdc +/-10%; Heater: 44 Vac
--------------	--

Max. power consumption	Mixing valve: 4 W (max.); Heater: 150 W (nominal)
------------------------	--

Technical specifications subject to change without notice.

For dimensional drawings and hook-up diagrams please visit the [product page](#) on our [website](#)

---

## Recommended accessories



### E-8000 SERIES

#### Digital Readout / Control Systems

Bright, wide angle, 1.8" display (TFT technology)

User friendly operation, menu driven with 4 push buttons

---

## Related products



**CEM EVAPORATOR W-101A**

Max. 2 g/h liquid;  
Max. 4 l/min gas  
Pressure rating 100 bar  
Very stable vapour flow  
Flexible gas/liquid ratio



**CEM EVAPORATOR W-102A**

Max. 30 g/h liquid;  
Max. 4 l/min gas  
Pressure rating 100 bar  
Very stable vapour flow  
Flexible gas/liquid ratio



**CEM EVAPORATOR W-303B**

Max. 1200 g/h liquid;  
Max. 100 l/min gas  
Pressure rating 100 bar  
Very stable vapour flow  
Flexible gas/liquid ratio



**BRONKHORST HIGH-TECH B.V.**

Nijverheidsstraat 1A

NL-7261 AK Ruurlo (NL)

Tel. +31 573 45 88 00

[info@bronkhorst.com](mailto:info@bronkhorst.com)