

GASFLOWMETING VAN INDUSTRIËLE GASSEN A065

APPLICATION NOTE A065-GP99

Industrial gas ammonia

The digital MASS-STREAM D-6300 series mass flow meters and controllers of Bronkhorst provide the most feasible solution for industrial gases like Ammonia (NH_3) with demanding characteristics.

Our mass flow meters and integrated controllers are equipped with stainless steel body (grade SS 316L) and EPDM sealing material. They can be used for gas flows up to 740 l/min NH_3 or up to 1000 l/min Air equivalent. The CTA (Constant Temperature Anemometry) thru-flow measurement with our inline sensor (no by-pass) is less sensitive to contamination.



Application requirements


- Robustness
- Contamination resistivity
- High repeatability
- Easy to check actual flow
- Ingress protection class IP65

Industrial sectors

- Heat treatment
- NOx reduction in exhaust fumes
- Cooling applications
- Catalyst processes
- Fermenters

Optional features

- Multi-functional displays
- Additional interface
- Up to 8 calibration curves in one instrument
- Pressure rating up to 20 bar (g)
- Compression type fittings



Flow scheme

Recommended Products



MASS-STREAM D-6370 MFM

Min. flow 2...100 l/min
Max. flow 10...1000 l/min
Drukklasse tot 20 bar
Robuuste sensor en behuizing (IP65)
Optioneel geïntegreerd TFT display



MASS-STREAM D-6341 MFC

Min. flow 0,14...7 l/min
Max. flow 1...50 l/min
Drukklasse tot 20 bar
Robuuste sensor en behuizing (IP65)
Optioneel geïntegreerd TFT display

Wil je meer informatie over flowmeters of -regelaars?

Wil je het laatste nieuws ontvangen over trends in flow control? Schrijf je dan in voor onze maandelijkse nieuwsbrief.



BRONKHORST NEDERLAND

Lunet 10c

3905 NW Veenendaal

Tel. [+31 \(0\)318 55 12 80](tel:+3120318551280)

info@bronkhorst.nl