


FLOWREGELING VOOR SUBATMOSFERISCHE TOEPASSING A066

APPLICATION NOTE A066-GP99

Sub-atmospheric

Bronkhorst offers digital MASS-STREAM D-6300 mass flow meters and integrated flow controllers for gases with flow rates from 0,2 up to 5000 l/min Air equivalent.

The CTA (Constant Temperature Anemometry) inline measurement principle incorporates effectively an open pipe allowing mass flow measurement and control also with pressure ratings below 1 bar(a).



Application requirements


- $P_1 > \text{approximately } 300 \text{ mbar (a)}$
- Integrated valve control with optional valve function 'fails in place' in case of a power failure
- Gas flow suction through the instrument can be generated with a pump
- Process evaluation with a trial unit before final order placement

Industrial sectors

- Process
- Low pressure
- Vacuum
- Testing
- Research

Optional features

- Multi-functional displays
- Additional interface
- Up to 8 calibration curves in one instrument
- Degreased instruments for oxygen applications



Flow scheme

Recommended Products



MASS-STREAM D-6370 MFM

Min. flow 2...100 l/min
Max. flow 10...1000 l/min
Drukklasse tot 20 bar
Robuuste sensor en behuizing (IP65)
Optioneel geïntegreerd TFT display



MASS-STREAM D-6380 MFM

Min. flow 10...500 l/min
Max. flow 50...5000 l/min
Drukklasse tot 20 bar
Robuuste sensor en behuizing (IP65)
Optioneel geïntegreerd TFT display

Wil je meer informatie over flowmeters of -regelaars?

Wil je het laatste nieuws ontvangen over trends in flow control? Schrijf je dan in voor onze maandelijkse nieuwsbrief.



BRONKHORST NEDERLAND

Lunet 10c

3905 NW Veenendaal

Tel. [+31 \(0\)318 55 12 80](tel:+3120318551280)

info@bronkhorst.nl