

MVM-001-PA

MAG-VIEW MVM-001-PA

Low-Flow Magnetic Inductive Flow meters for water-like liquids

- Compact, weatherproof (IP65) design
- No moving parts (no mechanical wear)
- Interference free operation
- Independence to inlet/outlet pipework
- Fast response
- Free pipe cross section: low ΔP , insensitive to contamination
- Analog output (4...20 mA)



MASSFLOW-ONLINE PRODUCT

Electromagnetic flow meters for low flow rates of water and aqueous solutions

MAG-VIEW instruments are electromagnetic inductive flow meters for electrically conductive liquids with a minimum conductivity of 50 $\mu S/cm$. The compact, weatherproof (IP65) flow meters do not contain any moving parts, cause virtually no pressure loss and can be mounted in any position, requiring no straight inlet or outlet runs.

MAG-VIEW flow meter model MVM-001-PA has a nominal diameter of DN2 for flow rates of 0,0083...1 l/min, suited for operating pressures up to 16 bar(g). The instrument allows frequency and analog output (4...20 mA) proportional to the flow.

Technische specificaties

Meet- / regelsysteem

Flow	0,0083 ... 1 l/min
Nauwkeurigheid volumeflowmeting	±1% RD at 0...50% of measuring range ±2% RD at 50...100% of measuring range (incl. fabriekskalibratiecertificaat; testcondities: water 23°C)
Turndown ratio	1:120
reproduceerbaarheid	1 % FS
Signaaluitgang vanaf	~ 0,005 l/min
Media	Water and other conductive liquids (minimum conductivity of 50 µS/cm)
Responstijd (sensor)	< 500 msec
Gemiddelde temperatuur	-20 ... 90 °C
Montage	Any position, attitude insensitive
Flow indicatie	green LED, flow proportional flashing

Mechanische delen

Materiaal (onderdelen die in contact komen met het medium)	Electrodes: Stainless Steel 1.4571 Process connections: Stainless Steel 1.4571 Measuring pipe: PEEK-GF30 Gasket: EPDM
Behuizing	Aluminium pressure diecasted
Diameter	DN2
Procesaansluitingen	1/4" BSP male thread
Beschermingsgraad (behuizing)	IP65
Nominale druk	PN16

Elektrische eigenschappen

Stroomvoorziening	24 Vdc ±10 %
Max. stroomverbruik	≤ 150 mA
Analoog signaal	4...20 mA, max. load 250 Ω to GND
Frequentie uitgang	Pulse rate / K-factor : 10000 pulses/l Resolution : 0,1 ml/pulse Signal shape : Square wave signal - duty cycle 50:50 Push-Pull - NPN open collector [o.c.] - PNP o.c. Signal current : max. 100 mA, current limited
Elektrische beveiligingsmaatregelen	Short-circuit proof, protected against polarity reversal
Elektrische aansluiting	5-pin-plug M12x1

Technische specificaties kunnen zonder kennisgeving worden gewijzigd.

Voor technische maattekeningen en aansluitschema's bezoekt u de [productpagina](#) op onze [website](#)

Related products



MAG-VIEW MVM-001-PN

Flow range 0,0083 ... 1 l/min
Pressure rating 16 bar
Non-obstructive; low ΔP
No moving parts; long life cycle
Pulse output



MAG-VIEW MVM-002-PA

Flow range 0,05 ... 2 l/min
Pressure rating 16 bar
Non-obstructive; low ΔP
No moving parts; long life cycle
Analog/Pulse output



MAG-VIEW MVM-002-PN

Flow range 0,05 ... 2 l/min
Pressure rating 16 bar
Non-obstructive; low ΔP
No moving parts; long life cycle
Pulse output



MAG-VIEW MVM-002-QA

Flow range 0,1 ... 2 l/min
Pressure rating 10 bar
Non-obstructive; low ΔP
No moving parts; long life cycle
Cost-optimized (plastic) model



BRONKHORST NEDERLAND

Lunet 10c

3905 NW Veenendaal

Tel. +31 (0)318 55 12 80

info@bronkhorst.nl